

Description

The MG 4860P No Clean Solder Paste is a no clean solder paste designed for surface mount applications using a syringe dispensing method. The post soldering residues of 4860P are non-conductive, non-corrosive and highly insulated.

Benefits

- Low residues
- Easily dispensed
- Excellent wettability
- Hard non-conductive residues

Solder Composition of MG 4860P Solder Paste

Sn63 alloy is the conventional eutectic solder used in most electronic assemblies. The Sn63 alloy conforms and exceeds the impurity requirements of J-STD-006 and all other relevant international standards.

Typical Analysis													
Sn	Pb	Cu	Ag	Sb	Bi	In	As	Fe	Ni	Cd	Al	Zn	Au
62.5-63.5	Bal.	0.030 Max	0.020 Max	0.050 Max	0.050 Max	0.050 Max	0.010 Max	0.010 Max	0.005 Max	0.001 Max	0.001 Max	0.001 Max	0.002 Max

Particle Size

Sn63 alloy is 3(45-25µm and J-STD-005 powder distribution. Solder powder distribution is measured utilizing laser diffraction, optical analysis and sieve analysis. Careful control of solder powder manufacturing processes ensures the particles' shape are 95% spherical minimum (aspect ratio < 1.5) and that the alloy contains a typical maximum oxide level of 80 ppm.

Classification of Solder Powder by Particle Size

Powder Type	Fines	Majority	Coarse	Typical Mesh
3	<10% 20	>80% 25-45	>90% 45	0% 50
				325/500

Metal Loading

Typical metal loading for dispensing application is 87.0-88.0 %.

Properties

MG 4860P Sn63/Pb37	
Melting Point, °C	183 E
Hardness, Brinell	14HB
Coefficient of Thermal Expansion	24.7
Tensile Strength, psi	4442
Density, g/cc	8.42
Electrical Resistivity, (μohm-cm)	14.5
Electrical Conductivity, 104/ohm-cm	6.9
Yield Strength, psi	3950
Total Elongation, %	48
Joint Shear Strength, at 0.1mm/min 20 °C	23
Joint Shear Strength, at 0.1mm/min 100 °C	14
Creep Strength, N/mm ² at 0.1mm/min 20 °C	3.3

Property	Specification	Test Method
Flux Classification	REL0	JSTD-004
Copper Mirror	No removal of copper film	IPC-TM-650 2.3.32
Corrosion	Pass	IPC-TM-650 2.6.15
SIR		
JSTD-004	2.44 x 10 ¹⁰ ohms	IPC-TM-650 2.6.3.3
Bellcore (Telecordia)	4.10 x 10 ¹⁰ ohms	Bellcore GR-78-CORE 13.1.3
Electromigration	Pass	Bellcore GR-78-CORE 13.1.4
Post Reflow Flux Residue	45%	TGA Analysis
Acid Value	110	IPC-TM-650 2.3.13
Metal Loading	88%	IPC-TM-650 2.2.20
Viscosity		
Brookfield (1), kcps	400+/-10% kcps	IPC-TM-650 2.4.34 modified
Malcom (2), poise	850-1100	IPC-TM-650 2.4.34.3 modified
Slump Test		
25 °C, 0.63 vertical/horizontal	No bridges all spacings	IPC-TM-650 2.4.35
150 °C, 0.63 vertical/horizontal	No bridges all spacings	IPC-TM-650 2.4.35
25 °C, 0.33 vertical/horizontal	0.20 /0.20	IPC-TM-650 2.4.35
150 °C, 0.33 vertical/horizontal	0.20/0.20	IPC-TM-650 2.4.35
Solder Ball Test	Pass	IPC-TM-650 2.4.43
Tack		
Initial	85 gm	JIS Z 3284
Tack retention @ 24 hr	90 gm	JIS Z 3284
Tack retention @ 24 hr	82 gm	JIS Z 3284

Dispensing

	Needle inner	Diameter	Applicable powder
Needle Gauge	in.	µm	(mesh cut)
18	0.033	838	-200+325
20	0.023	584	-325+500
21	0.02	508	-325+500
22	0.016	406	-325+500
23	0.013	330	-325+500
25	0.01	254	-400+635

The clearance gap between the needle and the substrate affects the shape and quality of the dot dispensed. If the clearance is too little, the dot tends to be flattened out, and if too large, the dot tends to have long tailing.

Pressure

The pressure applied in the syringe should be kept at a minimum, and the proper head pressure kept in the range of 15-25 lb/in² (1.05-1.76 kg/cm²). In cases where a paste requires much higher pressure (more than 40 lb/in² or 2.82 kg/cm²) to dispense, the paste will become inconsistent and clogging may be expected. The external air pressure supply should be maintained constant.


Paste Application

Solder paste should be taken out of the refrigerator at least 3 to 6 hours prior to use. This will give the paste enough time to come to thermal equilibrium with the environment. The flow rate of paste in a dispensing application depends on viscosity, which can be altered by temperature change. If solder paste is purchased in syringes pre-mixing is not necessary due to the shear action produced from the dispensing.

Reflow

Best results have been achieved when MG 4860P is reflowed in a forced air convection oven with a minimum of 8 zones (top & bottom), however reflow is possible with a 4 zone oven (top & bottom).

The following is a recommended profile for a forced air convection reflow process. The melting temperature of the solder, the heat resistance of the components, and the characteristics of the PCB (i.e. density, thickness, etc.) determine the actual reflow profile.



Preheat Zone - The preheat zone, is also referred to as the ramp zone, and is used to elevate the temperature of the PCB to the desired soak temperature. In the preheat zone the temperature of the PCB is constantly rising, at a rate that should not exceed 2.5 C/sec. The oven's preheat zone should normally occupy 25-33% of the total heated tunnel length.

The Soak Zone - normally occupies 33-50% of the total heated tunnel length exposes the PCB to a relatively steady temperature that will allow the components of different mass to be uniform in temperature. The soak zone also allows the flux to concentrate and the volatiles to escape from the paste.

The Reflow Zone - or spike zone is to elevate the temperature of the PCB assembly from the activation temperature to the recommended peak temperature. The activation temperature is always somewhat below the melting point of the alloy, while the peak temperature is always above the melting point.

Cleaning

MG 4860P is a no clean formulation therefore the residues do not need to be removed for typical applications. If residue removal is desired, use MG 8241-T or 8241-W Isopropyl Alcohol Wipes.

Storage and Handling

Store refrigerated between 2-10°C [35-50°F] to minimize solvent evaporation, flux separation, and chemical activity. Storage of syringes is preferred in an upright position with tip down to prevent flux separation and air entrapment. Use at room temperature, warm up can be achieved by removing from refrigerator 3 hours before use, faster warm up can also be achieved by placing in a sealed container in a water bath at near ambient temperature for 30 minutes.

Directions

Unscrew cap from dispensing end and screw on dispensing needle. Remove end cap from plunger and insert plunger or attach to an automatic dispenser. The supplied plunger will be slightly loose to prevent draw back when removing.

Shelf Life

6 Months - (30-50°F/2-10°C)

Reusing Solder Paste

This is not normally recommended, because it typically generates more problems than it is worth. If you do decide to reuse solder paste, these pointers may be helpful. This paste should be tightly sealed and refrigerated. Then, the paste may be reused at a later date, provided that the paste has not separated or thickened significantly compared to its original properties. Storage of syringes is preferred in an upright position with tip down to prevent flux separation and air entrapment.

Working Environment

Solder paste performs best when used in a controlled environment. Maintaining ambient temperature of between 68-77°F (20-25 °C) at a relative humidity of 40-65% will ensure consistent performance and maximum life of paste.

Cleaning Misprint Boards

If you should have a misprinted board, the paste may be cleaned off manually with MG 8241 Alcohol Wipes.

Stencil Cleaning

Periodic cleaning of the stencil during production is recommended to prevent any paste from being deposited in unwanted areas of the board. Without stencil cleaning, solder balling will increase. We recommend a periodic dry wipe (every 5 to 10 boards) with an occasional MG 8241-T or 8241-W Alcohol Wipe (every 15 to 25 boards). When running fine pitch boards, the cleaning may need to become more frequent.



ISO 9001 Registered Quality System,
Burlington, Ontario, Canada QMI File # 004908

Sn63/Pb37 No Clean Solder Paste 4860P Technical Data Sheet

4860P

Disposal

MG 4860P should be stored in a sealed container and disposed of in accordance with state & local authority requirements.

Technical Support

Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at www.mgchemicals.com.

Email: support@mgchemicals.com

Phone: 1-800-340-0772 Ext. 30 (Canada, Mexico & USA)

1-905-331-1396 Ext. 30 (International)

Fax: 1-905-331-2862 or 1-800-340-0773

Mailing address: Manufacturing & Support
1210 Corporate Drive
Burlington, Ontario, Canada
L7L 5R6

Head Office
9347-193rd Street
Surrey, British Columbia, Canada
V4N 4E7

Warranty

M.G. Chemicals Ltd. warrants this product for 12 months from the date of purchase by the end user. M.G. Chemicals Ltd. makes no claims as to shelf life of this product for the warranty. The liability of M.G. Chemicals Ltd. whether based on its warranty, contracts, or otherwise shall in no case include incidental or consequential damage.

Disclaimer

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.