

Band-pass filter for spectral analyzers

BA3830S

The BA3830S is a 6 + 1 band band-pass filter for spectral analyzer displays with internal recording indicator output. All of the capacitors comprising the filter are internal capacitors, making it possible to significantly reduce the number of attached components. This enables configuration of compact sets with a high level of reliability.

●Applications

CD radio cassette players, mini-components, car stereos

●Features

- 1) Six internal band-pass filters for spectral analyzers
- 2) Internal input/output for recording indicators
- 3) Internal capacitors reduce the number of attachments.

●Absolute maximum ratings (Ta = 25°C)


Parameter	Symbol	Limits	Unit
Power supply voltage	V _{CC}	9	V
Power dissipation	P _d	600*	mW
Operating temperature	T _{opr}	−25~+75	°C
Storage temperature	T _{stg}	−55~+150	°C

* Reduced by 6.0mW for each increase in Ta of 1°C over 25°C.

●Recommended operating conditions (Ta = 25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit
Operating power supply voltage	V _{CC}	4.5	—	8.0	V

● Block diagram



●Electrical characteristics (unless otherwise noted, Ta = 25°C, V_{CC} = 5V, R_L = 10MΩ, R_{φ1} = 270kΩ, R_{φ2} = 270kΩ)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Coniditions
Quiescent current	I _o	—	3.8	5.2	mA	
Reference output level (LEVEL)	V _{ol}	−3	0	3	dB	V _{IN} = −30dBV, V _o = 1.5V (0dB) When f=center frequencies is input
Max. output level (LEVEL)	V _{olmax}	3.2	4.2	—	V	V _{IN} = −14dBV, When f=center frequencies is input
Reference output level (REC LEVEL)	V _{or}	−3	0	3	dB	V _{IN} = −30dBV, V _o = 1.5V (0dB) f=1kHz
Max. output level (REC LEVEL)	V _{olmax}	3.8	4.8	—	V	V _{IN} = −14dBV, f=1kHz
Output offset voltage	V _{off}	—	30	90	mV	With no signal
Center frequency 1	f ₀₁	49	63	77	Hz	V _{IN} = −30dBV
Center frequency 2	f ₀₂	117	150	183	Hz	V _{IN} = −30dBV
Center frequency 3	f ₀₃	257	330	403	Hz	V _{IN} = −30dBV
Center frequency 4	f ₀₄	0.78	1	1.22	kHz	V _{IN} = −30dBV
Center frequency 5	f ₀₅	2.55	3.3	4.03	kHz	V _{IN} = −30dBV
Center frequency 6	f ₀₆	7.8	10	12.2	kHz	V _{IN} = −30dBV
Input current when Reset pin is HIGH	I _{IN}	150	215	280	μA	V _{IN} = 5V
Threshold level when Reset pin is ON	V _{th}	—	1.4	1.8	V	
Threshold level when Reset pin is OFF	V _{th}	1.0	1.4	—	V	

*Q is set to 4.5.

©Not designed for radiation resistance.

●Measurement circuit





Fig.1

● Circuit operation

(1) LINE and REC input circuits

The LINE and REC input circuits are configured as differential amplifiers, and the gain can be set to any desired value using an external resistor. The input impedance is determined by the external resistor.



(Note: All resistance values in the internal circuit diagrams noted here are reference values.)

Fig.2





Fig.3

(2) Bias circuit

A bias voltage of $V_{CC}/2$ is applied to each of the circuits. Since the output stage uses a push-pull configuration, a stable bias source can be obtained.



(Note: All resistance values in the internal circuit diagrams noted here are reference values.)

Fig.4

(3) BPF circuit

This is a circuit that selects the required frequency component from the input signal and amplifies it. With this configuration, no external capacitor is needed. In addition, the center frequency is set based on the current, so f_{01} and f_{02} to f_{06} can be set individually, using separate external resistors (pins1 and 2).

Q is set to 4.5V (Typ.).




Fig.5

(4) DET circuit

This circuit carries out phase detection on the signal selected and amplified by the BPF, and holds it at the peak level. It is configured so that all of the capacitors are internal.

The charge that was charged by the internal capacitors in the DET circuit is set to be discharged at 75ms/V (Typ.), but in order to eliminate any effects of disparity, a reset circuit is also included.




Fig.6

(5) Output section circuit

The signal level held at peak level by the DET undergoes V/I conversion and is output. Since the next stage supports MOS (high-input impedance), there is a resistance of 33.9k Ω (44.3k Ω for REC output only) between the output pin and the GND in the IC, so the output value changes based on the input impedance.




Fig.7

●Electrical characteristic curves




Fig.9 Output vs. frequency




Fig.10 Input vs. output level
(f_{01} to f_{06} modes)





Fig.11 Input vs. output level
(REC mode)

●External dimensions (Units: mm)



SDIP18



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.