

## FEATURES

- Ø 0.230 mm active area
- Low noise
- High speed
- Miniaturized

## DESCRIPTION

The AD230-8-2G MINI is an Avalanche Photodiode Amplifier Hybrid containing a 0.042 mm<sup>2</sup> active area APD chip integrated with an internal transimpedance amplifier. Hermetically packaged in a TO-52 with a borosilicate glass window cap.

## APPLICATIONS

- Lidar
- Analytical instruments
- Medical equipment


## RoHS

2011/65/EU


## Absolute maximum ratings

Symbol	Parameter	Min	Max	Unit
T <sub>STG</sub>	Storage Temp	-55	+125	°C
T <sub>OP</sub>	Operating Temp	0	+60	°C
T <sub>SOLDERING</sub>	Soldering Temp	-	+240	°C
P	Power Dissipation	-	360	mW
V <sub>CC</sub>	Single Supply Voltage	+3.0	+5.5	V
I <sub>CC</sub>	Supply Current	-	63	mA

## Spectral response @ M = 100



## Schematic



## ELECTRO-OPTICAL CHARACTERISTICS @ 23° C (V<sub>CC</sub> = single supply +3.3V, R<sub>L</sub> = 100W unless otherwise specified)

Symbol	Characteristic	Test Condition	Min	Typ	Max	Unit
f <sub>-3dB</sub>	Frequency Response	-3dB @ 800 nm	---	2	---	GHz
S	Sensitivity*	λ = 800 nm; M = 100	---	100	---	mV/μW
I <sub>CC</sub>	Supply Current	Dark state	---	34	63	mA

\* Sensitivity = APD responsivity (0.45 A/W X 100 gain) x TIA gain (2.5K)

These devices are sensitive to electrostatic discharge. Please use ESD precautions when handling.

## Avalanche photodiode data @ 23 °C

Symbol	CharacteristicC	Test-condition	Min	Typ	Max	Unit
$I_D$	Dark Current	M = 100 (see note 1)	---	0.3	1.0	nA
C	Capacitance	M = 100 (see note 1)	---	1.2	---	pF
$V_{BR}$	Breakdown Voltage	$I_D = 2 \mu A$	80	---	120	V
	Temperature Coefficient of $V_{BR}$		---	0.45	---	V/K
	Responsivity	M = 100; $\lambda = 800 \text{ nm}$	45	50	---	A/W
$\Delta f_{3dB}$	Bandwidth	-3dB	---	2	---	GHz
$t_r$	Rise Time	M = 100; $\lambda = 905 \text{ nm}$ ; $R_L = 50 \Omega$	---	0.18	---	ns
	Optimum Gain		50	60	---	
	"Excess Noise" factor	M = 100	---	2.2	---	
	"Excess Noise" index	M = 100	---	0.2	---	
	Noise Current	M = 100	---	1.0	---	pA/Hz <sup>1/2</sup>
	Max Gain		200	---	---	
NEP	Noise Equivalent Power	M = 100; $\lambda = 800 \text{ nm}$	---	$1.0 \times 10^{-14}$	---	W/Hz <sup>1/2</sup>

Note 1: Measurement conditions: Setup of photo current 1 nA at M = 1 and irradiated by a 880 nm, 80 nm bandwidth LED. Increase the photo current up to 100 nA, (M = 100) by internal multiplication due to an increasing bias voltage.

## Transimpedance amplifier data @ 25 °C

( $V_{CC} = +3.0 \text{ V}$  to  $5.5 \text{ V}$ ,  $T_A = 0^\circ\text{C}$  to  $70^\circ\text{C}$ ,  $100\Omega$  load between OUT+ and OUT-. Typical values are at  $T_A = 25^\circ\text{C}$ ,  $V_{CC} = +3.3 \text{ V}$ )

Parameter	Test-condition	Min	Typ	Max	Unit
Supply Voltage		3	5	5.5	V
Supply Current		---	34	63	mA
Transimpedance	Differential, measured with $40 \mu A$ p-p signal	2.10	2.75	3.40	k $\Omega$
Output impedance	Single ended per side	48	50	52	$\Omega$
Maximum Differential Output Voltage	Input = 2 mA p-p with $100 \Omega$ differential termination	220	380	575	mV p-p
AC Input Overload		2	---	---	mA p-p
DC Input Overload		1	---	---	mA
Input Referred RMS Noise	TO-52 package, see note 3	---	490	668	nA
Input Referred Noise Density	See note 3	---	11	---	pA/Hz <sup>1/2</sup>
Small signal bandwidth	Source capacitance = $0.85 \text{ pF}$ , see note 2	1.525	2.00	---	GHz
Low Frequency Cutoff	-3 dB, input < $20 \mu A$ DC	---	30	---	kHz
Transimpedance Linear Range	Peak to peak $0.95 < \text{linearity} < 1.05$	40	---	---	$\mu A$ p-p
Power Supply Rejection Ratio (PSRR)	Output referred, $f < 2 \text{ MHz}$ , $\text{PSRR} = -20 \text{ Log} (\Delta V_{out} / \Delta V_{cc})$	---	50	---	dB

Note 2: Source capacitance for AD230-8-2G-MINI is the capacitance of APD.

Note 3: Input referred noise is calculated as RMS output noise/ (gain at  $f = 10 \text{ MHz}$ ). Noise density is (input referred noise)/vbandwidth.

## TRANSFER CHARACTERISTICS

The circuit used is an avalanche photodiode directly coupled to a high speed data handling transimpedance amplifier. The output of the APD (light generated current) is applied to the input of the amplifier. The amplifier output is in the form of a differential voltage pulsed signal.

The APD responsivity curve is provided in Fig. 2. The term Amps/Watt involves the area of the APD and can be expressed as Amps/mm<sup>2</sup>/Watts/mm<sup>2</sup>, where the numerator applies to the current generated divided by the area of the detector, the denominator refers to the power of the radiant energy present per unit area. As an example assume a radiant input of 1 microwatt at 850 nm. The APD's corresponding responsivity is 0.4 A/W.

If energy in =  $1 \mu W$ , then the current from the APD =  $(0.4 \text{ A/W}) \times (1 \times 10^{-6} \text{ W}) = 0.4 \mu A$ . We can then factor in the typical gain of the APD of 100, making the input current to the amplifier  $40 \mu A$ . From Fig. 5 we can see the amplifier output will be approximately 75 mV p-p.

## APPLICATION NOTES

The AD230-8-2G-MINI is a high speed optical data receiver. It incorporates an internal transimpedance amplifier with an avalanche photodiode. This device does not operate in DC mode or below 30 kHz.

This detector requires +3.0 V to +5.5 V voltage supply for the amplifier and a high voltage supply (100-240 V) for the APD. The internal APD follows the gain curve published for the AD230-8-TO52-S1 avalanche photodiode. The transimpedance amplifier provides differential output signals in the range of 200 millivolts differential. The APD gain is voltage and temperature dependent. Some form of temperature compensation bias voltage control may be required.

In order to achieve highest gain, the avalanche photodiode needs a positive bias voltage (Fig. 1). However, a current limiting resistor must be placed in series with the photodiode bias voltage to limit the current into the transimpedance amplifier. **Failure to limit this current may result in permanent failure of the device.** The suggested initial value for this limiting resistor is 390 KOhm.

When using this receiver, good high frequency placement and routing techniques should be followed in order to achieve maximum frequency response. This includes the use of bypass capacitors, short leads and careful attention to impedance matching. The large gain bandwidth values of this device also demand that good shielding practices be used to avoid parasitic oscillations and reduce output noise.

Fig. 1: APD gain vs bias voltage




Fig. 2: APD Spectral response (M = 1)




Fig. 3 : Differential output vs temperature




Fig.4 : APD capacitance vs voltage




Fig. 5: Amplifier transfer function





Fig. 6: Total frequency response





Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



#### Как с нами связаться

**Телефон:** 8 (812) 309 58 32 (многоканальный)

**Факс:** 8 (812) 320-02-42

**Электронная почта:** [org@eplast1.ru](mailto:org@eplast1.ru)

**Адрес:** 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.