

T H E R M O M E T R I C S  
A C O M M I T M E N T T O E X C E L L E N C E

# NTC

## Type FP07

### Thermometrics Fastip Probe Thermistor



The NTC Type FP Series Fastip Thermoprobes consist of small diameter glass-coated thermistor beads hermetically sealed at the tips of shock resistant glass rods. The small bead thermistor has a very thin glass coating which allows for relatively flat frequency response for flow applications. As much of the bead as possible is exposed at the tip of the glass rod to provide the fastest response times. The units are rugged and unaffected by severe environmental exposures, including high density nuclear radiation.

The NTC Type FP Series Fastip Thermoprobes are ideally suited for high speed measurement and control of fluid temperatures, fluid level or flow. They offer the ease of handling associated with large glass probe thermistors as well as ultra-fast response times of small glass coated bead thermistors. These units exhibit relatively flat response to flow input from 200 Hz to 1000 Hz.

#### Features

- Ultra-Fast Response Time
- Rugged, Unaffected by Severe Environmental Exposures
- Relatively Flat Frequency Response
- Ease of Handling

#### Applications

- Sub-Sea Monitoring
- High Speed Fluid Temperature Measurement & Control
- Industrial

**Amphenol**  
**Advanced Sensors**


# Type FP07 Specifications

## Thermal and Electrical Properties

The following table lists the thermal and electrical properties for all large ruggedized thermobeads. All definitions and test methods are per MIL-PRF-23648.

| Thermistor Type  |              | FP07                |  |
|------------------|--------------|---------------------|--|
| Maximum Diameter |              | 0.085 in. (22 mm)   |  |
| Body Length      |              | 0.5 in. (12.7 mm)   |  |
| Lead Wires       |              |                     |  |
| Nominal Diameter |              | 0.012 in. (0.30 mm) |  |
| Lead Length      |              | 0.875 in. (22 mm)   |  |
| Lead Material    |              | Tinned dumet        |  |
| Material System  |              |                     |  |
| Code Letter      | R vs T Curve | 25/125 Ratio        | Nominal Resistance Range (Ω) @ 77°F (25°C) |
| E                | 0            | 5.0                 | -  |
| A                | 1            | 11.8                | 300 to 600                                 |
| A                | 2            | 12.5                | 680 k to 1.6 k                             |
| A                | 3            | 14.0                | 1.6 k to 3.6 k                             |
| A                | 4            | 16.9                | 3.6 k to 6.8 k                             |
| A                | 5            | 19.8                | 6.8 k to 27 k                              |
| A                | 6            | 22.1                | -  |
| A                | 7            | 22.7                | 27 k to 75 k                               |
| B                | 8            | 29.4                | 75 k to 130 k                              |
| B                | 9            | 30.8                | 130 k to 240 k                             |
| B                | 10           | 32.3                | 240 k to 360 k                             |
| B                | 11           | 35.7                | 360 k to 820 k                             |
| B                | 12           | 38.1                | 820 k to 13 M                              |
| B                | 13           | 45.0                | 1.3 M to 3.3 M                             |
| B                | 14           | 48.1                | 3.3 M to 6.8 M                             |
| B                | 15           | 56.5                | 6.8 M to 10 M                              |
| D                | 16           | 75.6                | -  |
| D                | 17           | 81.0                | -  |

Resistance vs temperature characteristics: The nominal resistance range for the zero-power resistance at 77°F (25°C) is shown for each thermobead type and each available material system. Each material system is denoted by an ordering code letter, a referenced curve number and the nominal 77°F/257°F (25°C/125°C) resistance ratio.



NTC Type FP07 Dimensions

| Thermistor Time Constant    | FP07        |
|-----------------------------|-------------|
| Still Air at 77 °F (25°C)   | 0.10 sec    |
| Plunge into Water           | 7 msec      |
| Dissipation Constant        |             |
| Still Air at 77 °F (25°C)   | 0.05 mW/°C  |
| Still Water at 77 °F (25°C) | 0.25 mW/°C  |
| Power Rating (in air)       |             |
| Maximum Power Rating        | 0.006 Watts |

## Ordering Information

The code number to be ordered may be specified as follows:

| Code | Model Number                                |
|------|---|
| FP   | 07  |
|      | Code  |
|      | D   |
|      | Probe Length                                |
|      | 0.5 (12.7 mm)                               |
|      | (Other lengths available on special order)  |
|      | Code  |
|      | X   |
|      | Material System Code                        |
|      | See Thermal and Electrical Properties table |
|      | Code  |
|      | 103   |
|      | Zero Power Resistance                       |
|      | See note below*                             |
|      | Code  |
|      | Tolerance @ 77°F (25°C)**                   |
|      | F   |
|      | 1   |
|      | G   |
|      | 2   |
|      | J   |
|      | 5   |
|      | K   |
|      | 10  |
|      | L   |
|      | 15  |
|      | M   |
|      | 20  |
|      | N   |
|      | 25  |
|      | P   |
|      | 30  |
|      | Q   |
|      | 40  |
|      | R   |
|      | 50  |
|      | S   |
|      | Non-standard (consult factory)              |
| FP   | ___   |
|      | ___   |
|      | ___   |
|      | ___   |
|      | ___   |
|      | Typical model number                        |

\*The zero-power resistance at 77°F (25°C), expressed in ohms (Ω), is identified by a three digit number. The first two digits represent significant figures and the last digit specifies the number of zeros to follow. Example: A Fastip probe with a 7 msec response time in water, 10 kΩ ±25% at 77°F (25°C) would be coded FP07DA103N.

\*\*Special tolerances are available on request. To specify a non-standard tolerance, use the letter 'S' followed by the desired tolerance (i.e., S7 = ±7%).

# Amphenol

## Advanced Sensors

[www.amphenol-sensors.com](http://www.amphenol-sensors.com)

© 2014 Amphenol Corporation. All Rights Reserved. Specifications are subject to change without notice. Other company names and product names used in this document are the registered trademarks or trademarks of their respective owners.



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



#### Как с нами связаться

**Телефон:** 8 (812) 309 58 32 (многоканальный)

**Факс:** 8 (812) 320-02-42

**Электронная почта:** [org@eplast1.ru](mailto:org@eplast1.ru)

**Адрес:** 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.