Dual retriggerable monostable multivibrator with reset

Rev. 10 — 3 December 2015

Product data sheet

1. General description

The 74HC123; 74HCT123 are high-speed Si-gate CMOS devices and are pin compatible with Low-power Schottky TTL (LSTTL). They are specified in compliance with JEDEC standard no. 7A.

The 74HC123; 74HCT123 are dual retriggerable monostable multivibrators with output pulse width control by three methods:

- 1. The basic pulse is programmed by selection of an external resistor (R_{EXT}) and capacitor (C_{EXT}).
- 2. Once triggered, the basic output pulse width may be extended by retriggering the gated active LOW-going edge input (nĀ) or the active HIGH-going edge input (nB). By repeating this process, the output pulse period (nQ = HIGH, nQ = LOW) can be made as long as desired. Alternatively an output delay can be terminated at any time by a LOW-going edge on input nRD, which also inhibits the triggering.
- 3. An internal connection from nRD to the input gates makes it possible to trigger the circuit by a HIGH-going signal at input nRD as shown in <u>Table 3</u>.

Schmitt-trigger action in the $n\overline{A}$ and nB inputs, makes the circuit highly tolerant to slower input rise and fall times.

The 74HC123; 74HCT123 are identical to the 74HC423; 74HCT423 but can be triggered via the reset input.

2. Features and benefits

- DC triggered from active HIGH or active LOW inputs
- Retriggerable for very long pulses up to 100 % duty factor
- Direct reset terminates output pulse
- Schmitt-trigger action on all inputs except for the reset input
- ESD protection:
 - HBM JESD22-A114F exceeds 2000 V
 - MM JESD22-A115-A exceeds 200 V
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

nexperia


Dual retriggerable monostable multivibrator with reset

3. Ordering information

Table 1. Ordering information

Type number	Package			
	Temperature range	Name	Description	Version
74HC123D	–40 °C to +125 °C	SO16	plastic small outline package; 16 leads;	SOT109-1
74HCT123D	_		body width 3.9 mm	
74HC123DB	–40 °C to +125 °C	SSOP16	plastic shrink small outline package; 16 leads;	SOT338-1
74HCT123DB	_		body width 5.3 mm	
74HC123PW	–40 °C to +125 °C	TSSOP16	plastic thin shrink small outline package; 16 leads;	SOT403-1
74HCT123PW			body width 4.4 mm	
74HC123BQ	–40 °C to +125 °C	DHVQFN16	plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body $2.5 \times 3.5 \times 0.85$ mm	SOT763-1


4. Functional diagram




74HC_HCT123
Product data sheet

74HC123; 74HCT123

Dual retriggerable monostable multivibrator with reset






Product data sheet

Dual retriggerable monostable multivibrator with reset

5. Pinning information



5.1 Pinning

5.2 Pin description

Symbol	Pin	Description	
1Ā	1	negative-edge triggered input 1	
1B	2	positive-edge triggered input 1	
1RD	3	direct reset LOW and positive-edge triggered input 1	
1 <u>Q</u>	4	active LOW output 1	
2Q	5	active HIGH output 2	
2CEXT	6	external capacitor connection 2	
2REXT/CEXT	7	external resistor and capacitor connection 2	
GND	8	ground (0 V)	
2Ā	9	negative-edge triggered input 2	
2B	10	positive-edge triggered input 2	
2RD	11	direct reset LOW and positive-edge triggered input 2	
2 Q	12	active LOW output 2	
1Q	13	active HIGH output 1	
1CEXT	14	external capacitor connection 1	
1REXT/CEXT	15	external resistor and capacitor connection 1	
V _{CC}	16	supply voltage	

Dual retriggerable monostable multivibrator with reset

6. Functional description

Table 3. Function table ^[1]	
--	--

Input			Output	
nRD	nĀ	nB	nQ	nQ
L	Х	Х	L	Н
Х	Н	Х	L ^[2]	H[2]
Х	Х	L	L ^[2]	H[2]
Н	L	\uparrow	Л	J
Н	\downarrow	Н	Л	U
1	L	Н	Л	U

[1] H = HIGH voltage level; L = LOW voltage level; X = don't care; \uparrow = LOW-to-HIGH transition; \downarrow = HIGH-to-LOW transition;

= one HIGH level output pulse; \Box = one LOW level output pulse.

[2] If the monostable was triggered before this condition was established, the pulse will continue as programmed.

7. Limiting values

Table 4.Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{CC}	supply voltage			-0.5	+7	V
I _{IK}	input clamping current	V_{I} < -0.5 V or V_{I} > V_{CC} + 0.5 V		-	±20	mA
I _{OK}	output clamping current	V_{O} < -0.5 V or V_{O} > V_{CC} + 0.5 V		-	±20	mA
I _O	output current	except for pins nREXT/CEXT; $V_{O} = -0.5 \text{ V}$ to ($V_{CC} + 0.5 \text{ V}$)		-	±25	mA
I _{CC}	supply current			-	50	mA
I _{GND}	ground current			-	-50	mA
T _{stg}	storage temperature			-65	+150	°C
P _{tot}	total power dissipation	SO16 package	<u>[1]</u>	-	500	mW
		SSOP16 package	[2]	-	500	mW
		TSSOP16 package	[2]	-	500	mW
		DHVQFN16 package	[3]	-	500	mW

[1] For SO16 package: P_{tot} derates linearly with 8 mW/K above 70 °C.

[2] For SSOP16 and TSSOP16 packages: P_{tot} derates linearly with 5.5 mW/K above 60 °C.

[3] For DHVQFN16 package: Ptot derates linearly with 4.5 mW/K above 60 °C.

Unit

V V

V

ns/V

ns/V

ns/V

°C

Dual retriggerable monostable multivibrator with reset

8. Recommended operating conditions

Symbol	Parameter	Conditions	7	74HC12	3	74HCT123		
			Min	Тур	Max	Min	Тур	Max
V _{CC}	supply voltage		2.0	5.0	6.0	4.5	5.0	5.5
VI	input voltage		0	-	V _{CC}	0	-	V _{CC}
Vo	output voltage		0	-	V _{CC}	0	-	V _{CC}
$\Delta t / \Delta V$	input transition rise and	nRD input						
	fall rate	V _{CC} = 2.0 V	-	-	625	-	-	-
		V _{CC} = 4.5 V	-	1.67	139	-	1.67	139
		$V_{CC} = 6.0 V$	-	-	83	-	-	-
T _{amb}	ambient temperature		-40	+25	+125	-40	+25	+125

Table 5. Recommended operating conditions

9. Static characteristics

Table 6. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		25 °C		-40 °C to	o +85 °C	-40 °C to	o +125 ℃	Unit
			Min	Тур	Max	Min	Max	Min	Max	
74HC123	3	I					1			-
VIH	HIGH-level	V _{CC} = 2.0 V	1.5	1.2	-	1.5	-	1.5	-	V
	input voltage	$V_{CC} = 4.5 V$	3.15	2.4	-	3.15	-	3.15	-	V
		V _{CC} = 6.0 V	4.2	3.2	-	4.2	-	4.2	-	V
VIL	LOW-level	V _{CC} = 2.0 V	-	0.8	0.5	-	0.5	-	0.5	V
	input voltage	$V_{CC} = 4.5 V$	-	2.1	1.35	-	1.35	-	1.35	V
		V _{CC} = 6.0 V	-	2.8	1.8	-	1.8	-	1.8	V
V _{OH}	HIGH-level	$V_{I} = V_{IH} \text{ or } V_{IL}$								
	output voltage	$I_{O} = -20 \ \mu A; \ V_{CC} = 2.0 \ V$	1.9	2.0	-	1.9	-	1.9	-	V
		I_{O} = -20 μ A; V_{CC} = 4.5 V	4.4	4.5	-	4.4	-	4.4	-	V
		$I_{O} = -20 \ \mu A; \ V_{CC} = 6.0 \ V$	5.9	6.0	-	5.9	-	5.9	-	V
		$I_{O} = -4 \text{ mA}; V_{CC} = 4.5 \text{ V}$	3.98	4.32	-	3.84	-	3.7	-	V
		$I_{O} = -5.2 \text{ mA}; V_{CC} = 6.0 \text{ V}$	5.48	5.81	-	5.34	-	5.2	-	V
V _{OL}	LOW-level	$V_{I} = V_{IH} \text{ or } V_{IL}$								
	output voltage	$I_0 = 20 \ \mu A; V_{CC} = 2.0 \ V$	-	0	0.1	-	0.1	-	0.1	V
		$I_0 = 20 \ \mu A; V_{CC} = 4.5 \ V$	-	0	0.1	-	0.1	-	0.1	V
		$I_0 = 20 \ \mu A; V_{CC} = 6.0 \ V$	-	0	0.1	-	0.1	-	0.1	V
		$I_0 = 4 \text{ mA}; V_{CC} = 4.5 \text{ V}$	-	0.15	0.26	-	0.33	-	0.4	V
		$I_0 = 5.2 \text{ mA}; V_{CC} = 6.0 \text{ V}$	-	0.16	0.26	-	0.33	-	0.4	V
I	input leakage current	$V_{I} = V_{CC}$ or GND; $V_{CC} = 6.0 V$	-	-	±0.1	-	±1.0	-	±1.0	μA
I _{CC}	supply current		-	-	8.0	-	80	-	160	μA

Dual retriggerable monostable multivibrator with reset

Table 6. Static characteristics ...continued

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		25 °C		–40 °C t	o +85 °C	-40 °C to	o +125 ℃	Unit
			Min	Тур	Max	Min	Max	Min	Мах	
CI	input capacitance		-	3.5	-	-	-	-	-	pF
74HCT12	23									
V _{IH}	HIGH-level input voltage	V_{CC} = 4.5 V to 5.5 V	2.0	1.6	-	2.0	-	2.0	-	V
V _{IL}	LOW-level input voltage	V_{CC} = 4.5 V to 5.5 V	-	1.2	0.8	-	0.8	-	0.8	V
V _{OH}	HIGH-level	$V_{I} = V_{IH} \text{ or } V_{IL}; V_{CC} = 4.5 \text{ V}$								
	output voltage	I _O = -20 μA	4.4	4.5	-	4.4	-	4.4	-	V
		$I_0 = -4 \text{ mA}$	3.98	4.32	-	3.84	-	3.7	-	V
V _{OL}	LOW-level output voltage	$V_{I} = V_{IH} \text{ or } V_{IL}; V_{CC} = 4.5 \text{ V}$								
01		I _O = 20 μA	-	0	0.1	-	0.1	-	0.1	V
		I _O = 4.0 mA	-	0.15	0.26	-	0.33	-	0.4	V
I _I	input leakage current	$V_{I} = V_{CC}$ or GND; $V_{CC} = 5.5$ V	-	-	±0.1	-	±1.0	-	±1.0	μA
I _{CC}	supply current		-	-	8.0	-	80	-	160	μA
ΔI _{CC}	additional supply current	per input pin; $I_0 = 0 A$; $V_I = V_{CC} - 2.1 V$; other inputs at V_{CC} or GND; $V_{CC} = 4.5 V$ to 5.5 V								
		pins nĀ, nB	-	35	125	-	160	-	170	μΑ
		pin nRD	-	50	180	-	225	-	245	μΑ
CI	input capacitance		-	3.5	-	-	-	-	-	pF

Dual retriggerable monostable multivibrator with reset

10. Dynamic characteristics

Table 7. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V); $C_L = 50 \text{ pF}$ unless otherwise specified; for test circuit see <u>Figure 12</u>.

Symbol	Parameter	Conditions		25 °C		–40 °C t	o +85 °C	-40 °C t	o +125 °C	Unit
			Min	Тур	Max	Min	Max	Min	Max	-
74HC123	3									
t _{pd}	propagation delay	$ \begin{array}{l} n\overline{RD}, n\overline{A}, nB \text{ to } nQ \text{ or } n\overline{Q}; \\ C_{EXT} = 0 \text{ pF}; \\ R_{EXT} = 5 \text{ k}\Omega; \\ \text{see Figure 9} \end{array} $	[1]							
		V _{CC} = 2.0 V	-	83	255	-	320	-	385	ns
		V _{CC} = 4.5 V	-	30	51	-	64	-	77	ns
		$V_{CC} = 5 \text{ V}; \text{ C}_{L} = 15 \text{ pF}$	-	26	-	-	-	-	-	ns
		V _{CC} = 6.0 V	-	24	43	-	54	-	65	ns
		$ \begin{array}{l} n\overline{RD} \mbox{ (reset) to } nQ \mbox{ or } n\overline{Q}; \\ C_{EXT} = 0 \mbox{ pF}; \\ R_{EXT} = 5 \mbox{ k}\Omega; \\ see \mbox{ Figure 9} \end{array} $								
		$V_{CC} = 2.0 V$	-	66	215	-	270	-	325	ns
		$V_{CC} = 4.5 V$	-	24	43	-	54	-	65	ns
		$V_{CC} = 5 \text{ V}; \text{ C}_{L} = 15 \text{ pF}$	-	20	-	-	-	-	-	ns
		$V_{CC} = 6.0 V$	-	19	37	-	46	-	55	ns
tt	transition time	see Figure 9	[1]							
		$V_{CC} = 2.0 V$	-	19	75	-	95	-	110	ns
		$V_{CC} = 4.5 V$	-	7	15	-	19	-	22	ns
		$V_{CC} = 6.0 V$	-	6	13	-	16	-	19	ns
t _W	pulse width	nA LOW; see Figure 10								
		$V_{CC} = 2.0 V$	100	8	-	125	-	150	-	ns
		$V_{CC} = 4.5 V$	20	3	-	25	-	30	-	ns
		$V_{CC} = 6.0 V$	17	2	-	21	-	26	-	ns
		nB HIGH; see Figure 10								
		$V_{CC} = 2.0 V$	100	17	-	125	-	150	-	ns
		$V_{CC} = 4.5 V$	20	6	-	25	-	30	-	ns
		$V_{CC} = 6.0 V$	17	5	-	21	-	26	-	ns
		nRD LOW; see Figure 11								
		$V_{CC} = 2.0 V$	100	14	-	125	-	150	-	ns
		$V_{CC} = 4.5 V$	20	5	-	25	-	30	-	ns
		$V_{CC} = 6.0 \text{ V}$ nQ HIGH and nQ LOW; $V_{CC} = 5.0 \text{ V}$; see Figure 10 and 11	[2]	4	-	21	-	26	-	ns
		C _{EXT} = 100 nF; R _{EXT} = 10 kΩ	-	450	-	-	-	-	-	μS
		C _{EXT} = 0 pF; R _{EXT} = 5 kΩ	-	75	-	-	-	-	-	ns

74HC_HCT123

Product data sheet

Dual retriggerable monostable multivibrator with reset

Symbol	Parameter	Conditions		25 °C		–40 °C t	o +85 °C	-40 °C to	o +125 °C	Unit
			Min	Тур	Max	Min	Max	Min	Max	
t _{rtrig}	retrigger time	$\label{eq:rescaled_response} \begin{array}{l} n\overline{A}, \ nB; \ C_{EXT} = 0 \ pF; & \underline{31} \\ R_{EXT} = 5 \ k\Omega; \ V_{CC} = 5.0 \ V; \\ see \ \underline{Figure \ 10} \end{array}$	<u>1</u> -	110	-	-	-	-	-	ns
R _{EXT}	external timing	see Figure 7								
	resistor	V _{CC} = 2.0 V	10	-	1000	-	-	-	-	kΩ
		$V_{CC} = 5.0 V$	2	-	1000	-	-	-	-	kΩ
C _{EXT}	external timing capacitor	g $V_{CC} = 5.0 \text{ V}; \text{ see } \frac{\text{Figure 7}}{\text{Figure 7}}$ [4]		-	-	-	-	-	-	pF
C _{PD}	power dissipation capacitance	per monostable; V _I = GND to V _{CC}	<u>5]</u> -	54	-	-	-	-	-	pF
74HCT12	23	1						•		
t _{PHL}	HIGH to LOW propagation delay	$n\overline{RD}$, $n\overline{A}$, nB to nQ or $n\overline{Q}$; $C_{EXT} = 0 pF$; $R_{EXT} = 5 k\Omega$; see Figure 9								
		V _{CC} = 4.5 V	-	30	51	-	64	-	77	ns
		$V_{CC} = 5 \text{ V}; \text{ C}_{L} = 15 \text{ pF}$	-	26	-	-	-	-	-	ns
		V _{CC} = 4.5 V	-	27	46	-	58	-	69	ns
		V _{CC} = 5 V; C _L = 15 pF	-	23	-	-	-	-	-	ns
t _{PLH}	LOW to HIGH propagation delay	$n\overline{RD}$, $n\overline{A}$, nB to nQ or $n\overline{Q}$; $C_{EXT} = 0 pF$; $R_{EXT} = 5 k\Omega$; see Figure 9								
		V _{CC} = 4.5 V	-	28	51	-	64	-	77	ns
		$V_{CC} = 5 \text{ V}; \text{ C}_{L} = 15 \text{ pF}$	-	26	-	-	-	-	-	ns
		$\overline{\text{NRD}}$ (reset) to nQ or $\overline{\text{NQ}}$; $C_{\text{EXT}} = 0 \text{ pF}$; $R_{\text{EXT}} = 5 \text{ k}\Omega$; see Figure 9								
		V _{CC} = 4.5 V	-	23	46	-	58	-	69	ns
		V _{CC} = 5 V; C _L = 15 pF	-	23	-	-	-	-	-	ns
t _t	transition time	$V_{CC} = 4.5 \text{ V}; \text{ see Figure 9}$	<u>l</u> -	7	15	-	19	-	22	ns

Table 7. Dynamic characteristics ... continued

Dual retriggerable monostable multivibrator with reset

Symbol	Parameter	Conditions			25 °C		–40 °C t	o +85 °C	–40 °C te	o +125 ℃	Unit
				Min	Тур	Max	Min	Max	Min	Max	
t _W	pulse width	V _{CC} = 4.5 V									
		nA LOW; see Figure 10		20	3	-	25	-	30	-	ns
		nB HIGH; see Figure 10		20	5	-	25	-	30	-	ns
		nRD LOW; see Figure 11		20	7	-	25	-	30	-	ns
		nQ HIGH and $n\overline{Q}$ LOW; V _{CC} = 5.0 V; see <u>Figure 10</u> and <u>11</u>	[2]								
		C_{EXT} = 100 nF; R_{EXT} = 10 k Ω		-	450	-	-	-	-	-	μS
		C _{EXT} = 0 pF; R _{EXT} = 5 kΩ		-	75	-	-	-	-	-	ns
t _{rtrig}	retrigger time	$eq:rescaled_$	<u>[3][4]</u>	-	110	-	-	-	-	-	ns
R _{EXT}	external timing resistor	$V_{CC} = 5.0 \text{ V}; \text{ see } \frac{\text{Figure 7}}{100000000000000000000000000000000000$		2	-	1000	-	-	-	-	kΩ
C _{EXT}	external timing capacitor	$V_{CC} = 5.0 V$; see <u>Figure 7</u>	[4]	-	-	-	-	-	-	-	pF
C _{PD}	power dissipation capacitance	per monostable; V _I = GND to V _{CC} $-$ 1.5 V	<u>[5]</u>	-	56	-	-	-	-	-	pF

Table 7. Dynamic characteristics ...continued

Voltages are referenced to GND (ground = 0 V); $C_L = 50 \text{ pF}$ unless otherwise specified; for test circuit see Figure 12.

[1] t_{pd} is the same as t_{PHL} and t_{PLH} ; t_t is the same as t_{THL} and t_{TLH}

[2] For other R_{EXT} and C_{EXT} combinations see Figure 7. If $C_{EXT} > 10$ nF, the next formula is valid.

 $t_W = K \times R_{EXT} \times C_{EXT}$, where:

 t_W = typical output pulse width in ns;

 R_{EXT} = external resistor in k Ω ;

C_{EXT} = external capacitor in pF;

K = constant = 0.45 for V_{CC} = 5.0 V and 0.55 for V_{CC} = 2.0 V.

The inherent test jig and pin capacitance at pins 15 and 7 (nREXT/CEXT) is approximately 7 pF.

[3] The time to retrigger the monostable multivibrator depends on the values of R_{EXT} and C_{EXT} . The output pulse width will only be extended when the time between the active-going edges of the trigger input pulses meets the minimum retrigger time. If C_{EXT} >10 pF, the next formula (at V_{CC} = 5.0 V) for the setup time of a retrigger pulse is valid:

 t_{rtrig} = 30 + 0.19 \times R_{EXT} \times $C_{EXT}^{0.9}$ + 13 \times $R_{EXT}^{1.05},$ where:

t_{rtrig} = retrigger time in ns;

 C_{EXT} = external capacitor in pF; R_{EXT} = external resistor in k Ω .

The inherent test jig and pin capacitance at pins 15 and 7 (nREXT/CEXT) is 7 pF.

- [4] When the device is powered-up, initiate the device via a reset pulse, when $C_{EXT} < 50$ pF.
- [5] C_{PD} is used to determine the dynamic power dissipation (P_D in μ W).

 $P_{D} = C_{PD} \times V_{CC}^{2} \times f_{i} + \sum (C_{L} \times V_{CC}^{2} \times f_{o}) + 0.75 \times C_{EXT} \times V_{CC}^{2} \times f_{o} + D \times 16 \times V_{CC} \text{ where:}$

f_i = input frequency in MHz;

 $f_o = output frequency in MHz;$

D = duty factor in %;

 C_L = output load capacitance in pF;


 V_{CC} = supply voltage in V;

$$\begin{split} &C_{EXT} = \text{timing capacitance in pF}; \\ &\sum (C_L \times V_{CC}^2 \times f_0) \text{ sum of outputs.} \end{split}$$

74HC HCT123


74HC123; 74HCT123

Dual retriggerable monostable multivibrator with reset




Dual retriggerable monostable multivibrator with reset


11. Waveforms



74HC123; 74HCT123

Dual retriggerable monostable multivibrator with reset





74HC123; 74HCT123

Dual retriggerable monostable multivibrator with reset




Table 8. Test data


Туре	Input		Load	Load				
	VI	t _r , t _f	CL	RL	t _{PHL} , t _{PLH}			
74HC123	V _{CC}	6 ns	15 pF, 50 pF	1 kΩ	open			
74HCT123	3 V	6 ns	15 pF, 50 pF	1 kΩ	open			

Dual retriggerable monostable multivibrator with reset

12. Application information


12.1 Timing component connections

The basic output pulse width is essentially determined by the values of the external timing components R_{EXT} and $C_{\text{EXT}}.$



12.2 Power-up considerations


When the monostable is powered-up it may produce an output pulse, with a pulse width defined by the values of R_{EXT} and C_{EXT} . This output pulse can be eliminated using the circuit shown in Figure 14.



Dual retriggerable monostable multivibrator with reset

12.3 Power-down considerations

A large capacitor C_{EXT} may cause problems when powering-down the monostable due to the energy stored in this capacitor. When a system containing this device is powered-down or a rapid decrease of V_{CC} to zero occurs, the monostable may sustain damage, due to the capacitor discharging through the input protection diodes. To avoid this possibility, use a damping diode (D_{EXT}) preferably a germanium or Schottky type diode able to withstand large current surges and connect as shown in Figure 15.



Dual retriggerable monostable multivibrator with reset

13. Package outline




Fig 16. Package outline SOT109-1 (SO16)

Dual retriggerable monostable multivibrator with reset




Fig 17. Package outline SOT338-1 (SSOP16)

All information provided in this document is subject to legal disclaimers.

Dual retriggerable monostable multivibrator with reset





Fig 18. Package outline SOT403-1 (TSSOP16)

All information provided in this document is subject to legal disclaimers.

Dual retriggerable monostable multivibrator with reset



DHVQFN16: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 x 3.5 x 0.85 mm SOT763-1

Fig 19. Package outline SOT763-1 (DHVQFN16)

All information provided in this document is subject to legal disclaimers.

Dual retriggerable monostable multivibrator with reset

14. Abbreviations

Table 9.Abbreviations	
Acronym	Abbreviation
CMOS	Complementary Metal Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model
LSTTL	Low-power Schottky Transistor-Transistor Logic
MM	Machine Model

15. Revision history

Table 10. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes	
74HC_HCT123 v.10	20151203	Product data sheet	-	74HC_HCT123 v.9	
Modifications:	Type numbers 74HC123N and 74HCT123N (SOT38-4) removed.				
74HC_HCT123 v.9	20150119	Product data sheet	-	74HC_HCT123 v.8	
Modifications:	• <u>Table 7</u> : Powe	er dissipation capacitance cond	dition for 74HCT123	is corrected.	
74HC_HCT123 v.8	20111216	Product data sheet	-	74HC_HCT123 v.7	
Modifications:	Legal pages updated.				
74HC_HCT123 v.7	20110825	Product data sheet	-	74HC_HCT123 v.6	
74HC_HCT123 v.6	20110314	Product data sheet	-	74HC_HCT123 v.5	
74HC_HCT123 v.5	20090713	Product data sheet	-	74HC_HCT123 v.4	
74HC_HCT123 v.4	20060616	Product data sheet	-	74HC_HCT123 v.3	
74HC_HCT123 v.3	20040511	Product specification	-	74HC_HCT123_CNV v.2	
74HC_HCT123_CNV v.2	19980708	Product specification	-	-	

Dual retriggerable monostable multivibrator with reset

16. Legal information

16.1 Data sheet status

Document status[1][2]	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

16.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any

representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and

customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

16.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof. Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - Nexperia

products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Product data sheet

Dual retriggerable monostable multivibrator with reset

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of

non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the

product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond

Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

16.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

17. Contact information

For more information, please visit: http://www.nexperia.com

For sales office addresses, please send an email to: salesaddresses@nexperia.com

74HC123; 74HCT123

Dual retriggerable monostable multivibrator with reset

18. Contents

1	General description 1
2	Features and benefits 1
3	Ordering information 2
4	Functional diagram 2
5	Pinning information 4
5.1	Pinning 4
5.2	Pin description 4
6	Functional description 5
7	Limiting values 5
8	Recommended operating conditions 6
9	Static characteristics 6
10	Dynamic characteristics 8
11	Waveforms 12
12	Application information 15
12.1	Timing component connections 15
12.2	Power-up considerations 15
12.3	Power-down considerations 16
13	Package outline 17
14	Abbreviations 21
15	Revision history 21
16	Legal information 22
16.1	Data sheet status 22
16.2	Definitions
16.3	Disclaimers
16.4	Trademarks 23
17	Contact information 23
18	Contents 24



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный) Факс: 8 (812) 320-02-42 **Электронная почта:** <u>org@eplast1.ru</u> **Адрес:** 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.