








ALIGNMENT TOLERANCE FOR .100 MAX. BOARD-TO-BOARD MISALIGNMENT
(NO CONNECTOR FLOAT)




PANEL-TO-P.C. BOARD
APPLICATION #1



PANEL-TO-P.C. BOARD
APPLICATION #2



PANEL-TO-P.C. BOARD
APPLICATION #3



P.C. BOARD-TO-P.C. BOARD
APPLICATION #4

SEE SHEET 1 EC NO: UCP2012-3041 DRWN: NGUYEN CHKD: JELL APPR: FSMITH P2	2012/06/28 2012/06/28 2012/07/03	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY RJF	DATE 01-25-89	TITLE SELECTIVELY LOADED RECEPTACLE HEADER ASSY (MINI-FIT JR. SERIES)  MOLEX INCORPORATED			
				4 PLACES	± .005	± .005	CHECKED BY BAP	DATE 01-25-89				
				3 PLACES	± .010	± .010	APPROVED BY RAS	DATE 01-25-89				
				2 PLACES	± 0.25	± .015	MATERIAL NO.	DOCUMENT NO.				SHEET NO.
				1 PLACE	± 0.38	± .005	SEE CHART					SDA-42416-*
				ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

	13	12	11	10	9	8	7	6	5	4	3	2	1																																																																																					
J	PART NO.	ENG. NO.	CKT. SIZE	HSG. MAT'L.	TERMINAL PLATING REQUIRED AT EACH CIRCUIT LOCATION: - = VOIDED CIRCUIT																																																																																													
					1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24																																																																						
	I5-24-8 I4 I	A-424 I6- I4BA	I4	94V-0	-	A	-	A	-	A	-	A	-	A	-	A	-	A	-	A	-	A	-	A	-	A	-	A																																																																						
	I5-24-8 I45	A-424 I6- I4BB	I4	94V-0	A	-	-	A	-	A	-	-	A	-	A	-	-	A	-	-	-	-	-	-	-	-	-																																																																							
I	I5-24-8 I5 I	A-424 I6- I4BC	I4	94V-0	A	-	-	A	-	A	A	-	A	-	A	-	A	A	-	-	-	-	-	-	-	-	-																																																																							
	I5-24-8 I52	A-424 I6- I4BD	I4	94V-0	A	A	-	A	-	A	A	A	A	-	A	-	A	A	-	-	-	-	-	-	-	-																																																																								
	424 I6-000 I	-----	06	94V-2	A	-	A	-	A	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-																																																																								
H	424 I6-0002	-----	10	94V-2	-	A	-	A	-	A	-	A	A	A	-	-	-	-	-	-	-	-	-	-	-	-																																																																								
	424 I6-0003	-----	06	94V-0	A	-	A	A	-	A	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-																																																																									
	424 I6-0004	-----	24	94V-2	-	-	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A																																																																								
	424 I6-0005	-----	14	94V-0	A	V	A	V	A	V	A	A	V	A	V	A	V	A	-	-	-	-	-	-	-	-																																																																								
	424 I6-0006	-----	18	94V-0	A	V	V	A	V	V	A	A	A	A	V	V	A	V	V	A	A	A	-	-	-	-																																																																								
G																													G																																																																					
F																													F																																																																					
E																													E																																																																					
D																													D																																																																					
C																													C																																																																					
B																													B																																																																					
A																													A																																																																					
					LEGEND: <u>CIRCUIT SIZE</u> (02-24) _____ <u>HOUSING MATERIAL</u> _____ A = 94V-2,NATURAL B = 94V-0,NATURAL <u>VOID CIRCUIT VARIATION</u> _____ A-424 I6-***																																																																																													
					<table><tr><td rowspan="5">SEE SHEET 1 EC NO: UCP2012-3041 2012/06/28 DRWN:NGUYEN 2012/06/28 CHKD:JBELL 2012/07/03 APPR:FSMITH</td><td rowspan="5">DESCRIPTION REV</td><td>QUALITY SYMBOLS</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE</td><td>SCALE</td><td>DESIGN UNITS</td><td rowspan="5"></td><td rowspan="5">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td colspan="2">IN/MM</td><td></td><td></td><td></td><td></td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY</td><td>DATE</td><td colspan="2" rowspan="3">SELECTIVELY LOADED RECEPTACLE HEADER ASSY (MINI-FIT JR. SERIES)</td></tr><tr><td></td><td></td><td></td><td>CHECKED BY</td><td>DATE</td></tr><tr><td></td><td></td><td></td><td>BAP</td><td>01-25-89</td></tr><tr><td></td><td></td><td></td><td colspan="2">ANGULAR ±1/2°</td><td>APPROVED BY</td><td>DATE</td><td colspan="2">MOLEX INCORPORATED</td></tr><tr><td></td><td></td><td></td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SEE CHART</td><td colspan="2">DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr><td></td><td></td><td></td><td colspan="2"></td><td colspan="2">SIZE</td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="2">3 OF 3</td></tr></table>																				SEE SHEET 1 EC NO: UCP2012-3041 2012/06/28 DRWN:NGUYEN 2012/06/28 CHKD:JBELL 2012/07/03 APPR:FSMITH	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS		THIRD ANGLE PROJECTION		IN/MM							mm	INCH	DRAWN BY	DATE	SELECTIVELY LOADED RECEPTACLE HEADER ASSY (MINI-FIT JR. SERIES)					CHECKED BY	DATE				BAP	01-25-89				ANGULAR ±1/2°		APPROVED BY	DATE	MOLEX INCORPORATED					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		DOCUMENT NO.		SHEET NO.							SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					3 OF 3						
SEE SHEET 1 EC NO: UCP2012-3041 2012/06/28 DRWN:NGUYEN 2012/06/28 CHKD:JBELL 2012/07/03 APPR:FSMITH	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS		THIRD ANGLE PROJECTION																																																																																								
			IN/MM																																																																																															
			mm	INCH	DRAWN BY	DATE	SELECTIVELY LOADED RECEPTACLE HEADER ASSY (MINI-FIT JR. SERIES)																																																																																											
					CHECKED BY	DATE																																																																																												
					BAP	01-25-89																																																																																												
			ANGULAR ±1/2°		APPROVED BY	DATE	MOLEX INCORPORATED																																																																																											
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		DOCUMENT NO.		SHEET NO.																																																																																									
					SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					3 OF 3																																																																																						
1b_frame_C_P_AM_T Rev. F 2009/06/18					12	11	10	9	8	7	6	5	4	3	2	1																																																																																		



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.