

## New EVAL\_PAN1026EMK PAN1026 Experimenter Kit



### Accelerate Development Using Panasonic's PAN1026 Series *Bluetooth* RF Module!


Introducing a new development tool to the PAN1026 family, the PAN1026 Experimenter Kit supplements Panasonic's evaluation kit (EVAL\_PAN1026) by emulating an application environment where a Bluetooth RF module is controlled by an external processor, an environment that reduces both software and hardware development time. This kit is for design engineers using Panasonic's PAN1026 Bluetooth SmartReady® RF Module with embedded Bluetooth Classic and Bluetooth Low Energy protocol stacks and profiles and based on Toshiba's TC35661, baseband controller and ARM7TDMI CPU SOC.

The PAN1026 Experimenter Kit integrates a PAN1026 RF module<sup>1</sup>, Toshiba's TMPM369 ARM Cortex-M3 based MCU with 512KB flash memory and serial, USB, CAN and Ethernet interfaces on a single board to eliminate hardware prototyping in the project's development stages<sup>2</sup>. A J-Link JTAG debugger interface incorporated in the Experimenter kit board is compatible with commonly available third party toolchains such as those from Atollic, IAR and Keil. The embedded MCU also supports standard interfaces on the board for Ethernet, CAN, USB (host and device), serial and UART connection.

The embedded dual mode Bluetooth Classic and Bluetooth Low Energy protocol stacks and profiles may be accessed using two command sets. Toshiba's TCU command set consisting of over 100 commands is extremely flexible, allowing full access to the PAN1026's resources and I/O. A superset of the TCU commands, (TCU Superset – TCUS) where one command executes a routine of TCU commands to perform common BT functions, is available using an Abstract Application Programming Interface – A2PI. The A2PI resides and executes Experimenter Kit's Cortex-M3 MPU.

1. This design is intended only for software development and should not be used as hardware reference design. For optimum performance, the module should be on the edge of the application PCB. For layout recommendations and how to place the module refer to the PAN1026 design guide.

2. The EVAL\_PAN1026 evaluation kit remains as an excellent demonstration and development tool for a PC based environment. The kit consists of two PAN1026ETU development modules used with EasySPP and EasyBLE testware. EasySPP is the development environment for Bluetooth Classic and EasyBLE is the development environment for Bluetooth Low Energy, both applications are available on Panasonic's website.



### Experimenter Kit Contents

- Toshiba TOPAS369BT Board
- Segger J-Link JTAG/SWD Emulator with USB interface including J-Link 19-pin Cortex-M Adapter and USB Cable

### Suggested IDEs


- Keil MDK™ with µVision® IDE/Debugger
- IAR® Kickstart Edition
- Atollic® TrueStudio® Lite

### Application Examples

Application examples are available that can be compiled to run on the TMPM369 MCU with FreeRTOS™. (The operating system is available from Real Time Engineers Ltd). The application software includes a set of BLE standard reference profiles and a design guide on how to develop a proprietary BLE profiles.

- SPP Over BLE Application
- BLE Heart Rate Measurement Over BLE Application

## EVAL\_PAN1026EMK Physical Interfaces



## PAN1026 Technical Characteristics

Parameter	Value	Condition
Receiver Sensitivity	-87 dBm typ.	Ideal Signal
Output Power	+4 dBm typ.	@ 50 Ohm Antenna Pin
Power Supply	1.7 to 3.6 V	Single Voltage Operation
Transmit	46 mA	ACL, DH1
Receive	46 mA	ACL, DH1
Operating Temperature	-40 to +85°C	

## Additional Information

For detailed specification information on the **EVAL\_PAN1026EMK** or the **PAN1026** Place and Play *Bluetooth* Module, visit our website at:

<http://www.panasonic.com/rfmodules/>



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



#### Как с нами связаться

**Телефон:** 8 (812) 309 58 32 (многоканальный)

**Факс:** 8 (812) 320-02-42

**Электронная почта:** [org@eplast1.ru](mailto:org@eplast1.ru)

**Адрес:** 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.