



Reduce risk of carpal tunnel syndrome!

Heyco® Lockit™ Strain Relief Pre-Assembly Equipment

Pre-Assembly Equipment for Heyco Assembly-Friendly Lockit Series Strain Reliefs:
RDD Lockits – for Double D and Round Mounting Holes.

ST Lockits – for Rectangular Mounting Holes.

Pre-Assemble Lockits onto cable for faster final assembly!

Watch this equipment in action at www.Heyco.com

Click on our Strain Relief Bushings Section and then the video Evolution of the Heyco Strain Relief Bushing in the upper left square.



A Headlock™ for RDD and ST Lockits

Assembly head for RDD and ST Lockit Strain Reliefs. Simply place a Lockit Strain Relief into the U opening of the assembly head. Then place the cable into the bushing body and close the head to secure the Lockit™ Strain Relief permanently onto the wire. This completed sub-assembly can then be installed with fingertip pressure into the application's mounting hole—at a later time, in a different place, for lower installed cost!



B FootLock™

Assembly machine for RDD and ST Lockit Strain Reliefs. This foot-pedal activated assembly machine is identical to Autolock™, except that the gravity fed track is loaded by hand instead of by a vibratory bowl.



C Autolock™ Semi-Automatic

Assembly machine for RDD and ST Lockit Strain Reliefs. Suitable for high volume production runs where batched sub-assemblies are desirable. Includes vibratory feeder bowl, track and head. The operator simply inserts the cable into the assembly head slot, then presses the foot pedal to secure the Strain Relief permanently onto the wire. This completed sub-assembly can be installed with fingertip pressure into the application's mounting hole—at a later time, in a different place, for lower installed cost!

Equipment for European requirements (motor power ratings and shielding) available, consult Heyco.

NEW! **D** RDD Lockit™ Guillotine - for fastest final assembly!

Optional guillotine type cutting attachment (not pictured) for the RDD Footlock™ and Autolock™ application equipment. The Lockit™ Guillotine removes the RDD hinge after attachment to the cable, thus reducing the clearance required for easy installation of the RDD/cable assembly, into the panel.

For Part No. and ordering, please consult Heyco.

For Lockit Strain Relief Hand Pliers see page 4-16.



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.