


HIGH FREQUENCY LEADED • BUILT-IN CAPACITORS, INDUSTRIAL GRADE CERAMIC RESONATORS AWCR Series



FEATURES:

- Excellent environmental resistance, Low cost.
- High-stability, Washable type
- Low cost timing solution.
- Built-in capacitors save space & components.
- Small size , Light weight

APPLICATIONS:

- Microprocessor clocks.
- Automotive controllers.
- Electric appliances.
- Industrial controllers.
- Remote controls.
- General timing.

STANDARD SPECIFICATIONS


Frequency Range (MHz)	Frequency Tolerance (at 25°C)	Frequency Stability (at -20°C to 80°C)	Resonant Impedance (Ω) max.	Operating temperature	Aging (10 yrs)	IC Tested	Vdd
1.8 ~ 6.00	±0.5%	±0.3%	100 for 1.80 ≤ F < 3.0 50 for 3.0 ≤ F < 3.5 30 for 3.5 ≤ F ≤ 6.0	See table 2	±0.3%	MC14069UBP	5V
6.01 ~ 13.00	±0.5%	±0.3%	30	See table 2	±0.3%	MC14069UBP	12V
13.01 ~ 50.00	±0.5%	±0.3%	40	See table 2	±0.3%	TC74HCU04	5V

Storage temperature: -40°C to +125°C
Environmental and mechanical specifications, see appendix C. Group 6.
Marking, see appendix G. Recommended handling, see appendix F.
Application notes, see appendix A.
Ammo packing, see appendix H.(1,500 pcs/box)

ORDERING OPTIONS

AWCRXX.XXMX - Packaging

Frequency in MHz - Ammo (ammo packing)
S, D or A



U1: MC14069UBP
74HCU04
Y1: RESONATOR

Built-in C1 C2: 30pF ± 20% (1.8M ~ 20.0MHz)
15pF ± 20% (20.01M ~ 25.99MHz)
5pF ± 20% (26.0M ~ 50MHz)

Dimensions: Inches (mm)

1	Input
2	Ground
3	Output




Table 1

Freq. (MHz)	H (max.)
1.8 ~ 6.0	0.315 (8.0)
6.01 ~ 50.0	0.395(10.0)

Table 2

Series	Operating temperature
MS	-20°C to +80°C
MD	-40°C to +85°C
MA	-40°C to +125°C

(Freq.stability ~ ± 0.5% typ.)
(Freq.stability ~ ± 0.7% typ.)

NOTE: Left blank if standard • All specifications and markings subject to change without notice

ABRACON IS
ISO 9001 / QS 9000
CERTIFIED

29 Journey • Aliso Viejo, CA 92656 • USA
(949) 448-7070 • FAX: (949) 448-8484

E-MAIL: abinfo@abracon.com • INTERNET ADDRESS: www.abracon.com

ABRACON
CORPORATION

41

Rev. B
01/2003

Washability Specification

This product can be washed using the following solvents under the suggested conditions:

Solvents:
HCFC, Isopropyl Alcohol, Trichloroethane, Tap water, Demineralized Water, Pine Alpha ST-100S
Ultrasonic Wash:
Less than 1 min. (Frequency:28KHz,Ouput:20W/L) Immersion Wash or others: Less than 5 min.
Solvents temperature should be at 60°C or under 60°C
Drying:
By air blow at 80°C max.



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.