

I 2 3 4

A

B

C

D

DIM X ± 0.2 ON TIP
 ± 0.13 ON BASE

2.0 ± 0.2 ON TIP
 ± 0.13 ON BASE TYP

DIM Y REF

NOTE 3

4.0

NOTE 4

2.00 ± 0.13

NOTE 5



0.50 ± 0.02 SQ PIN

DIM A


DIM B

1.5

1.5



CONFIDENTIAL

www.fciconnect.com			surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 		MM 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	KH LEE	2006-06-01	ANGULAR	LINEAR	0.X	±-	size A3	Scale 8:1			
Eng	KH LEE	2006-06-01			0.XX	±0.25					
Chr	KH LEE	2009-12-02	0°	±3°	0.XXX	±-	ECN		S10-0205		
Appr	JOEY NG	2009-12-02	Product family				MINITEK	Spec ref -			
		title	MINITEK II R/R SMT STR DUPEX HDR				dwg no	10069527		Rev. E	
			catalog no				-	CUSTOMER		sheet 1 of 2	

rev	ecn no	dr	date
A	S06-0192	KHL	2006-06-01
B	S06-0233	KHL	2006-07-10
C	S06-0385	KHL	2006-11-21
D	S07-0081	KHL	2007-03-01
E	S10-0205	PR	2009-12-02
-	-	-	-
-	-	-	-

REV F - 2006-04-17

I 2

3

PDM: Rev:E STATUS:Released Printed: Dec 21, 2010

A

B

C

D



Copyright FCI.



Copyright FCI.



14. A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

- NOTES:
- MATERIAL:
BODY : GLASS FILLED PCT UL 94V-0 (REFER TO TABLE FOR COLOR)
PIN : PHOSPHOR BRONZE
 - TOLERANCE UNLESS OTHERWISE NOTED ± 0.25
 - DIM 1.0 ± 0.15 FOR MOLDED SIDE(S) ONLY. IF SIDE(S) ARE BROKEN, DIM 1.5 MAX APPLIES
 - RECESS APPLIES TO MOLDED SIDE(S) ONLY.
 - POLARISATION BY OMISSION OF PIN. POSITION REFER TO TABLE
 - STANDARD PACKAGING IN PLASTIC BAG.
 - P/N 10069527-XXXTC TO BE PACKED IN TUBE WITH PICK-UP CAP INSTALLED IN THE CENTRE OF PRODUCT. SEE FIG. 1. REFER TO TABLE FOR AVAILABILITY.
 - P/N 10069527-XXXT TO BE PACKED IN TUBE. REFER TO TABLE FOR AVAILABILITY.
 - P/N 10069527-XXXTR TO BE PACKED WITH TAPE AND REEL (OPTIONAL: PICK-UP CAP). FCI MUST BE CONTACTED FOR AVAILABILITY IN SIZE REQUESTED.
 - SOLDER TAIL PLATING:
 $2.54\mu\text{m}$ MIN 100% MATTE TIN PLATING OVER $1.27\mu\text{m}$ MIN NICKEL UNDERPLATE.
 - PRODUCT DESCRIPTION CODE:
XXXXXXXX - XXXLF
LEAD FREE SEE NOTE 12 & 13
EXTENSION NUMBER
BASE NUMBER

12. THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN..

13. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

PICK-UP CAP






FIG. 1



RECOMMENDED PAD LAYOUT

CONFIDENTIAL

www.fciconnect.com			surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 		MM 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	KH LEE	2006-06-01	ANGULAR LINEAR		0.X		±-		size A3	Scale 8:1	
Eng	KH LEE	2006-06-01			0.XX		±0.25				
Chr	KH LEE	2009-12-02			0°	±3°	0.XXX				±-
Appr	JOEY NG	2009-12-02	Product family				MINITEK		Spec ref -		
		title MINITEK 11 R/R SMT STR DUPEX HDR				dwg no 10069527				Rev. E	
		catalog no				-		CUSTOMER		sheet 2 of 2	



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.