


| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
| AF  | 50   |           | AB1 | REVISED PER ECO-11-004820 | 11MAR11 | RK  | HMR  |

- 1 OPERATION TEMPERATURE IS 105° C MAX.
- 2 RETENTION FORCE - 16 OUNCES MIN INITIALLY.  
6 OUNCES MIN AFTER 500 CYCLES.
- 3 REFER TO MOUNTING HOLE PATTERN.
- 4 .175 MAX TO BE MEASURED ACROSS THE CUT-OFF TABS.



|          |                   |                |            |
|----------|-------------------|----------------|------------|
|          | NYLON 6/6; WHITE  | BRASS - GOLD   | 3-582118-9 |
| OBSOLETE | NYLON 6/6; GRAY   | BRASS - GOLD   | 3-582118-8 |
|          | NYLON 6/6; VIOLET | BRASS - GOLD   | 3-582118-7 |
|          | NYLON 6/6; BLUE   | BRASS - GOLD   | 3-582118-6 |
|          | NYLON 6/6; GREEN  | BRASS - GOLD   | 3-582118-5 |
|          | NYLON 6/6; YELLOW | BRASS - GOLD   | 3-582118-4 |
|          | NYLON 6/6; ORANGE | BRASS - GOLD   | 3-582118-3 |
|          | NYLON 6/6; RED    | BRASS - GOLD   | 3-582118-2 |
| OBSOLETE | NYLON 6/6; BROWN  | BRASS - GOLD   | 3-582118-1 |
|          | NYLON 6/6; BLACK  | BRASS - GOLD   | 3-582118-0 |
|          | NYLON 6/6; WHITE  | BRASS - SILVER | 2-582118-9 |
| OBSOLETE | NYLON 6/6; GRAY   | BRASS - SILVER | 2-582118-8 |
| OBSOLETE | NYLON 6/6; VIOLET | BRASS - SILVER | 2-582118-7 |
|          | NYLON 6/6; BLUE   | BRASS - SILVER | 2-582118-6 |
| OBSOLETE | NYLON 6/6; GREEN  | BRASS - SILVER | 2-582118-5 |
| OBSOLETE | NYLON 6/6; YELLOW | BRASS - SILVER | 2-582118-4 |
| OBSOLETE | NYLON 6/6; ORANGE | BRASS - SILVER | 2-582118-3 |
|          | NYLON 6/6; RED    | BRASS - SILVER | 2-582118-2 |
| OBSOLETE | NYLON 6/6; BROWN  | BRASS - SILVER | 2-582118-1 |
|          | NYLON 6/6; BLACK  | BRASS - SILVER | 2-582118-0 |
|          | NYLON 6/6; WHITE  | BRASS - TIN    | 1-582118-9 |
| OBSOLETE | NYLON 6/6; GRAY   | BRASS - TIN    | 1-582118-8 |
| OBSOLETE | NYLON 6/6; VIOLET | BRASS - TIN    | 1-582118-7 |
| OBSOLETE | NYLON 6/6; BLUE   | BRASS - TIN    | 1-582118-6 |
|          | NYLON 6/6; GREEN  | BRASS - TIN    | 1-582118-5 |
|          | NYLON 6/6; YELLOW | BRASS - TIN    | 1-582118-4 |
| OBSOLETE | NYLON 6/6; ORANGE | BRASS - TIN    | 1-582118-3 |
|          | NYLON 6/6; RED    | BRASS - TIN    | 1-582118-2 |
| OBSOLETE | NYLON 6/6; BROWN  | BRASS - TIN    | 1-582118-1 |
|          | NYLON 6/6; BLACK  | BRASS - TIN    | 1-582118-0 |

|                                        |  |                                |                              |                    |                        |                    |
|----------------------------------------|--|--------------------------------|------------------------------|--------------------|------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>M.S. FEHER<br>13APR2004 | TE Connectivity              |                    |                        |                    |
| DIMENSIONS:<br>mm                      |  | CHK<br>E. HOWARD<br>13APR2004  |                              |                    |                        |                    |
|                                        |  | APVD<br>E. HOWARD<br>13APR2004 | NAME<br>ASSEMBLY, TEST PROBE |                    |                        |                    |
|                                        |  | PRODUCT SPEC                   |                              |                    |                        |                    |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APPLICATION SPEC               |                              |                    |                        |                    |
| MATERIAL<br>SEE TABLE                  |  | WEIGHT<br>-                    | SIZE<br>A2                   | CAGE CODE<br>00779 | DRAWING NO<br>C=582118 | RESTRICTED TO<br>- |
| FINISH<br>SEE TABLE                    |  | CUSTOMER DRAWING               | SCALE<br>6:1                 | SHEET<br>1 of 1    | REV<br>AB1             |                    |

|          |                           |                               |             |
|----------|---------------------------|-------------------------------|-------------|
|          | -                         | -                             | -           |
|          | -                         | -                             | -           |
|          | -                         | -                             | -           |
|          | NYLON 6/6; NATURAL        | BRASS - GOLD                  | 6-582118-9  |
| OBSOLETE | NYLON 6/6; NATURAL        | BRASS - SILVER                | 5-582118-9  |
|          | HOUSING - MATERIAL; COLOR | RECEPTACLE - MATERIAL; FINISH | PART NUMBER |



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



#### Как с нами связаться

**Телефон:** 8 (812) 309 58 32 (многоканальный)

**Факс:** 8 (812) 320-02-42

**Электронная почта:** [org@eplast1.ru](mailto:org@eplast1.ru)

**Адрес:** 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.