


16 channels ± 100 V, $\pm 2/4$ A, 5/3-level RTZ, high-speed ultrasound pulser with integrated transmit beamformer



BGA144 ball (10x10x1 mm)

Features

- 0 to 200 V peak-to-peak output signal
- Up to 30 MHz operating frequency
- Power-up/down sequence free
- Gate driver self-biased architecture; no filtering capacitors required
- Pulsed wave (PW) mode operation:
 - 5/3 level output
 - ± 2 A / ± 4 A source and sink current
- Continuous wave (CW) mode operation:
 - 150 mW power consumption/channel
 - 270 fs RMS jitter (100 Hz-20 kHz)
 - -147 dBc/Hz @ 1 kHz phase noise
- Elastography mode operation
- Programmable fine-tuning delays to minimize second harmonic distortion
- Fully integrated real clamping-to-ground function
 - 11 Ω synchronous active clamp
 - ± 2 A source and sink current
- Fully integrated T/R switch
 - 9 Ω ON resistance
 - 28 pF parasitic capacitance
 - Compliant with receiver multiplexing function
- Auxiliary integrated circuits
 - Noise blocking diode function
 - Recirculation current protection
 - Anti-memory feature
 - Thermal protection
 - Undervoltage protection and bias supply checks
- Programmable power management to optimize the performance into a probe
- TX Beamforming in transmission mode
 - Programmable single-channel delay for beam steering and beam focusing
 - Clock frequency up to 200 MHz
 - Delay from 0 to 327 μ s with 5 ns of minimum resolution
 - 425 ns minimum delay table writing time
- Embedded memory to store transmission patterns
 - 65 kbits
 - Waveform compression algorithm
 - Up to 256 non repetitive states
 - Up to 4 states sequence repetition up to 2^{18} times
- Easy driving control
 - Control through serial interface
 - Few input signals to drive several devices
 - Single interrupt as alert signal
 - Fully automatic and programmable single trigger to manage TX/RX phases

Product status link	
STHV1600	
Product summary	
Order code	STHV1600
Package	BGA-144
Packing	Tray

- Anti-glitch on trigger signal during TX phase
- Checksum and parity check
- Very low package thermal resistance
- Latch-up free due to HV SOI technology
- Only a few passive components required
- LVDS/CMOS digital inputs

Applications

- Medical ultrasound imaging
- Pulse waveform generators
- NDT ultrasound transmission
- Piezoelectric transducer drivers

Description

This monolithic, high-voltage, high-speed pulse generator features 16 independent channels and integrates a 16-channel beamformer for pulse generation in multi-channel medical ultrasound applications targeted at low power portable systems.

A pure analog section provides each channel with voltage level translators, noise blocking diode function, two identical high voltage P-channel and two identical high voltage N-channel MOSFETs as the output stage (the two half bridges are called TX0 and TX1), clamping to-ground circuitry, anti-leakage, anti-memory block, thermal sensor, recirculation current protection and a T/R switch structure which guarantees effective isolation during the transmission phase.

Each channel can support up to five output levels with two independent half bridges. Both PW output stages (TX0 and TX1) are able to provide up to ± 2 A peak output current, independent from the HV power supply pins. The two half bridges can be driven in parallel with a current capability up to ± 4 A. The clamp circuit, used to carry the output pin XDCR to GND with a resistance of 11 Ω , has a current capability of up to 2 A during the transition. Each channel is provided with strong recirculation protection on the high voltage output node (XDCR) to preserve the device using inductive load without any external diode protection. The 16 independent T/R switches comprise an active circuit that can be used in both a dedicated RX chain per channel or in a multiplexing configuration.

The STHV1600 also includes some global blocks, thermal protection, undervoltage on VDDP3V3, VDDM3V3 and DVDD, POR on DVDD, global self-biased high-voltage MOSFET gate drivers with internal check of the correct value, and a check of the HV supply values. Twelve low voltage capacitors are included in the package. Ceramic capacitors are mandatory on the HV supplies and VDDP3V3 and VDDM3V3 on the PCB. The ball-out is designed to simplify application board routing and to prevent unexpected coupling between HV and LV.

All functions of the STHV1600 are managed by a digital core logic working at a maximum clock frequency of 200 MHz. This block is responsible for managing channel delay transmission used in beamformer, waveform generation and compression algorithm, store setting and data, managing all device operations in the correct sequence.

Starting from an IDLE state in which device can be configured by SPI interface and channels are in CLAMP state, transmission TX starts after the rising edge of the external trigger signal is provided. When transmission ends, a RX_WAIT state is performed, forcing channels in CLAMP state to clean signals from previous pulsing. The automatic receiving state, RX, starts and persists until a falling edge of the external trigger signal is provided, putting the device in the initial IDLE state. It also sets all configurations to perform transmission in continuous mode (CW) when a pulse sequence must be repeated indefinitely (until the falling edge of the trigger is provided) or pulse waves (PW) when a finite pulse sequence must be performed.

Revision history

Table 1. Document revision history

Date	Version	Changes
05-Jul-2018	1	Initial release.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.