

USB-2405

4-CH 24-Bit 128kS/s Dynamic Signal Acquisition USB 2.0 Module

NEW



Introduction

The USB-2405 is a 24-bit high-performance dynamic signal acquisition USB module equipped with 4 analog input channels providing simultaneous sampling at up to 128 kS/s per channel. The USB-2405 also features software-selectable AC or DC coupling input configuration and built-in high precision 2 mA excitation current to measure integrated electronic piezoelectric (IEPE) sensors such as accelerometers and microphones.

The USB-2405 delivers high precision, DC and dynamic measurement performance with very low temperature drift. The onboard 24-bit Sigma-Delta ADC supports anti-aliasing filtering, suppressing modulator and signal out-of-band noise and providing usable signal bandwidth of the Nyquist rate, making it ideal for high dynamic range signal measurement in vibration and acoustic applications.

The USB-2405 supports digital and analog trigger sources and flexible trigger modes, including post, delay, middle, gated, and pre-triggering for efficient data acquisition with no need for post-processing. The USB-2405 is USB bus-powered and equipped with BNC connectors and removable spring terminals for easy device connectivity.

Features

- Hi-Speed USB 2.0
- USB bus powered
- 24-bit Sigma-Delta ADC with built-in anti-aliasing filter
- 4-CH simultaneous sampling analog inputs, up to 128kS/s
- AC or DC input coupling, software selectable
- Analog or digital triggering
- Supports 2mA excitation output on each analog input channel for IEPE sensor measurement
- Full auto-calibration
- Supporting Time-Frequency analysis software -- Visual Signal DAQ Express
- Supported Operating System
 - Windows 7/8 x64/x86
- Driver and SDK
 - LabVIEW, MATLAB, C/C++ , Visual Basic, Visual Studio, .NET
- Software Utility
 - U-Test, Visual Signal DAQ Express

Standard Shipped Accessories

- 4-pin removable spring terminal
- 2 M USB Type A to USB Mini-B cable with lockable connector



- Module stand
- Rail-mount kit



- The installation USB flash drive for Visual Signal DAQ Express



Software

Visualized Time-Frequency Analysis (TFA)

With Visual Signal DAQ Express, the included time-frequency analysis application developed by AnCAD, ADLINK's software alliance partner expert in machinery vibration analysis, the USB-2405 is easily configured to acquire data and perform analysis in seconds. Visual Signal DAQ Express is based on visualization of analysis function blocks, enabling convenient and quick construction of the required software function block using a visualized user interface, enabling complicated, multi-task analysis without any programming.

Visualized signal process and analysis functional block library

Visual Signal Express features a variety of signal process and analysis function blocks, including Filter, Mathematics, Transform, Convert, and Time-Frequency Analysis (TFA). These function blocks can be composed and linked to achieve multi-task analysis based on the data flow.

Real-Time viewer

For data/waveform display, the Viewer area can be divided into several sub-windows for multi-viewer display. Visual Signal Express supports channel viewer, time-frequency viewer, and X-Y plotting.



- The installation USB flash drive for Visual Signal DAQ Express is already attached to the shipment-ready ADLINK USB-2405 and it's free of charge. Users need only follow the instructions on the quick start guide to register on the website and activate their Visual Signal DAQ Express.
- For Visual Signal DAQ Express functions introduction, please download the user manual on <http://www.adlinktech.com/USB-2405/support>

Ready-to-Use ADLINK U-Test Utility

U-Test is a free ready-to-use testing program allowing configuration and test data acquisition with no programming required, provides easy out-of-the-box configuration and generation of simple functions.

- No programming necessary for operation and full function testing of ADLINK USB DAQ/DIO
- Intuitive interface for data monitoring and logging, waveform generation, and digital I/O control panel use as virtual instrument
- Data exportable to Microsoft Excel for offline analysis



Specifications

Analog Input

Channels	4 (simultaneous sampling)
ADC Resolution	24 Bit
ADC type	Delta-sigma
Sampling rate	1 kS/s to 128 kS/s
Input range	±10V
FIFO buffer size	2k samples per channel
Input Configuration	Differential or pseudo-differential
Input impedance	200 kΩ (between positive input and negative input) 16.93 kΩ (Between negative input and chassis ground)
Input coupling	AC or DC, software selectable
Integrated Electronic Piezoelectric (IEPE)	Current: 2 mA or 0 mA, software selectable IEPE compliance: 24V
Over-voltage protection	±60V
Input common mode range	±10V
Trigger source	Analog or digital, software selectable
Trigger mode	Post trigger, delay trigger, middle trigger, gated trigger, pre-trigger, post or delay trigger with re-triggering
Data Transfer	Programmed I/O, continuous (bulk transfer mode)

DC accuracy (25°C)

Offset Error (mV)	Gain Error (%)
Typical: ±0.15mV	Typical: ±0.15%
Max. ±0.3mV	Max. ±0.3%

AC Dynamic Performance (typical, 25°C)

- THD, THD+N (Vin = 8.9 Vpk)

Input configuration	Input Signal Frequency (fin)	THD	THD+N
Differential	20 Hz to 20 kHz	-94 dB	-91 dB
	20 Hz to 46.4 kHz	-89 dB	-88 dB
Pseudo-differential	20 Hz to 20 kHz	-92 dB	-88 dB
	20 Hz to 46.4 kHz	-85 dB	-85 dB

- CMRR

AC (20 Hz to 1 kHz)	60 dB
---------------------	-------

- Bandwidth

-3dB bandwidth	0.49 * sampling rate
AC cut-off frequency (-3dB)	0.4 Hz
AC cut-off frequency (-0.1dB)	2.4 Hz

- Flatness

Input Signal Frequency (fin)	Flatness
20 Hz to 20 kHz	±0.01 dB
20 Hz to 46.4 kHz	±0.15 dB

- Crosstalk

Input Signal Frequency (f _i)	Crosstalk
1 kHz	-102 dB
46.4 kHz	-95 dB

- System noise

Mode	AI Noise
High-Resolution (< 52.734 kHz)	50µVrms
High-Speed Mode (52.734 kHz to 128 kHz)	65µVrms

- SFDR (Vin = -1 dBFS)

Input Signal Frequency (fin)	SFDR
1 kHz	104 dB

- Dynamic Range (Vin = -60 dBFS, fs = 102.4kS/s)

Input Signal Frequency (fin)	Dynamic range
1 kHz	100 dB

Digital Input / Output

Channels	2 programmable function I/O
Compatibility	3.3V / TTL (single-ended)
Initial status	Input (pull low)
Input voltage	Logic low: VIL = 0.8 V max; IIL = 0.2 mA max. Logic high: VIH = 2.0 V min.; IIH = 0.2 mA max.
Output voltage	Logic low: VOL = 0.8 V max; IOL = 0.2 mA max. Logic high: VOH = 2.0 V min.; IOH = 24 mA max.
Over-voltage protection	-2V ~ +7V
Supporting modes	<ul style="list-style-type: none"> • Static digital input/output • Pulse output, max. frequency: 4 MHz • Frequency/Event counter, max. frequency: 4MHz • Digital trigger IN • Synchronization sample clock IN
Data Transfer	Programmed I/O

Note: Function I/O shares the same I/O pins, such that only one of these modes can be selected at a time.

General Specifications

- I/O connector: Four BNC connectors and 4-pin removable spring terminals
- Operating temperature: 0 to 55°C (32 to 131°F)
- Storage temperature: -20 to 70°C (-4 to 158°F)
- Power requirements: 5V @ 400mA (USB bus powered)
- Dimensions (not including connectors and stand): 115 mm (W) x 150 mm (D) x 40 mm (H) (4.5" x 5.91" x 1.57")
- Relative humidity: 5% to 95%, non-condensing

Ordering Information

■ USB-2405

4-CH 24-Bit 128kS/s Dynamic Signal Acquisition
USB 2.0 Module

Optional Accessories

■ USB-2M-L

2 M USB Type A to USB Mini-B cable
with lockable connector

IO connector definition





Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.