



"If any part of the loop should open (become disconnected or have out of limit resistance), the circuit will go into the alarm state" [ref TR20.20], nonetheless, due to the redundancy inherent in the dual wire wrist strap design, the operator will continue to be grounded via the second intact wire.

Per ESD Handbook TR20.20 section 5.3.9.2.2 Dual Conductor Resistance Continuous Monitors, "This type of monitor is used with a two wire (dual conductor) wrist strap. The wrist strap assembly consists of a two-wire ground cord and a wristband that has two isolated halves. When a person is wearing the wrist strap properly, the monitor measures the loop resistance consisting of one wire of the ground cord, one-half of the wristband, the person's skin, the second half of the wristband, and a second wire in the ground cord. If any part of the loop should open (become disconnected or have out of limit resistance), the circuit will go into the alarm state.

ESD Handbook TR 20.20 paragraph 5.3.2.4.4 Test Frequency "Because wrist straps have a finite life, it is important to develop a test frequency that will guarantee integrity of the system. Typical test programs recommend that wrist straps that are used daily should be tested daily. However, if the products that are being produced are of such value that knowledge of a continuous, reliable ground is needed, and then continuous monitoring should be considered or even required"

Continuous Monitors pay for themselves improving quality, productivity, eliminating wrist strap daily testing and test result logging. Per ESD-S1.1 paragraph 6.1.3 Frequency of Functional Testing "Daily [Wrist Strap] testing may be omitted if constant monitoring is used."

Improve wrist strap contact with Reztore™ ESD Hand Lotion

Dual Wire Coil Cord provides redundancy; even if one conductor is severed, operator has reliable path-to-ground with other wire.

- Used with resistive loop technology continuous monitor, continuously verifies the proper resistance to ground of the operator
- Custom manufactured right angle mono-plug reduces chance of accidental disconnects providing more secure ground connection
- Coil cord with molded 1 Megohm current limiting resistor on both ground paths to protect user from shock due to inadvertent contact with line voltage
- 28 gauge wire
- 3.5mm phono plug connector
- Superior reliability. Greatly exceeds ESD S1.1 Bending Life Test. Tested at over 200,000 cycles vs. the 16,000 requirement
- Superior warranty - See details of 1 year Limited Warranty at <http://www.Desco.com/Warranty.aspx>

Use patented* Dual Wire Wrist Strap with Desco Dual Wire Continuous Monitor

ITEM	REF. #	DESCRIPTION
19868	SPR1106	6' Coil Cord, 7mm male snaps, right angle mono plug
19863	SE4040	12' Coil Cord, 7mm male snaps, right angle mono plug
19862	SE4033	6' Coil Cord, 4mm female snaps, right angle mono plug

*U.S. Patents 6,052,053 and 6,205,408

COIL CORD, DUAL-WIRE, DUAL-SNAP, RIGHT ANGLE MONO PLUG

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: Desco.com
PHONE (909) 627-8178 FAX (909) 627-7449
DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
PHONE (781) 821-8370 FAX (781) 575-0172

**DRAWING
NUMBER**
19868

DATE:
March
2009

DESCO



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.