

# 3M EPX™ Plus II Manual Applicator

## Directions for Use: 1:1 and 2:1 Mix Ratio Products

<p><b>1 Assemble Applicator</b></p> <p>1:1 2:1</p>	<p><b>2 Load 3M™ Scotch-Weld™ Adhesive Duo-Pak Cartridge</b></p> <p>1:1 2:1</p>	<p><b>3 Dispense and Discard a Small Amount of Adhesive to Assure Correct Ratio</b></p>	
<p><b>4 Cut for Desired Bead Size</b></p> <p>To Increase Adhesive Bead Size</p>	<p><b>5 Attach Mixing Nozzle</b></p>	<p><b>6 Apply Adhesive</b></p>	<p><b>7 Remove Cartridge</b></p>
<p><b>Plunger</b></p> <p>2:1 - 62-9170-9921-0</p> <p>1:1 - 62-9170-9911-1</p>	<p><b>Mixing Nozzles</b></p> <p>62-9742-9935-6</p> <p>or</p> <p>62-9171-9153-8</p>		

**IMPORTANT NOTICE:** 3M MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of application.

**LIMITATION OF REMEDIES AND LIABILITY:** If the 3M product is proved to be defective, THE EXCLUSIVE REMEDY, AT 3M'S OPTION, SHALL BE TO REFUND THE PURCHASE PRICE OF OR TO REPAIR OR REPLACE THE DEFECTIVE 3M PRODUCT. 3M shall not otherwise be liable for any loss or damages, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including negligence, warranty, or strict liability.

**3M**

**Engineered Adhesives Division**

3M Center, Building 220-7E-01  
St. Paul, MN 55144-1000  
1-800-364-3577 or 612-737-6501



Printed on 50% recycled  
paper, including 10%  
post-consumer waste.

Printed in U.S.A.

© 3M 2002 34-8515-6885-6



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



#### Как с нами связаться

**Телефон:** 8 (812) 309 58 32 (многоканальный)

**Факс:** 8 (812) 320-02-42

**Электронная почта:** [org@eplast1.ru](mailto:org@eplast1.ru)

**Адрес:** 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.