

Mounting Bracket Kit for Overhead Ionizers

Installation Instructions



Made in the
United States of America




Figure 1. Desco [60469](#) Mounting Bracket Kit for Overhead Ionizers

Description

The Desco [60469](#) Mounting Bracket Kit for Overhead Ionizers provides greater mounting flexibility than traditional hanging chains. Angle adjustment tension knobs are included to rotate and aim the ionizer directly at the area to be neutralized. Additional mounting hardware such as screws, bolts and nuts are not included.

The Desco [60469](#) Mounting Bracket Kit is compatible with the following Desco overhead ionizers:

Item	Description
50602	Chargebuster® Overhead Ionizer with Lights, 2-Fan, 220VAC
50603	Chargebuster® Overhead Ionizer with Lights, 3-Fan, 220VAC
50664	Overhead Zero Volt Ionizer, 2-Fan, 120VAC
50665	Overhead Zero Volt Ionizer, 3-Fan, 120VAC
50671	Overhead Zero Volt Ionizer, 2-Fan, 220VAC
50672	Overhead Zero Volt Ionizer, 3-Fan, 220VAC
50681	Chargebuster® Overhead Ionizer, 3-Fan, 220VAC
50682	Chargebuster® Overhead Ionizer, 2-Fan, 220VAC
60467	Chargebuster® Overhead Ionizer with Lights, 2-Fan, 120VAC
60468	Chargebuster® Overhead Ionizer with Lights, 3-Fan, 120VAC
60473	Chargebuster® Overhead Ionizer, 3-Fan, 120VAC
60640	Chargebuster® Overhead Ionizer, 2-Fan, 120VAC

Packaging

- 2 Mounting Brackets
- 2 Fluted Knobs
- 2 3-Arm Knobs
- 2 Rubber Spacers

Installation

1. Install the fluted knobs (A), mounting brackets (B), rubber spacers (C) and 3-arm knobs (D) to the mounting plates (E) located on both ends of the overhead ionizer.




Figure 2. Installing the Mounting Bracket Kit to the Overhead Ionizer

2. Determine the mounting location for the overhead ionizer, and use hardware (not included) to secure the mounting bracket kit in place.
3. Use the fluted knobs and 3-arm knobs to rotate and aim the overhead ionizer directly at the area to be neutralized.
4. Connect the overhead ionizer's power cord to its power receptacle. Route the power cord to the AC outlet, and plug it into the outlet.



Figure 3. Using the Mounting Bracket Kit on a workbench beam



Figure 4. Securing the Mounting Bracket Kit to an overhead beam




Figure 5. Using the Mounting Bracket Kit on workbench posts




Figure 6. Securing the Mounting Bracket Kit to posts

Specifications

Bracket Material	Stainless Steel
Dimensions	See Figure 7
Weight (per mounting bracket)	0.2 lbs. (91 g)
Country of Origin	United States of America




Figure 7. Dimensions of Mounting Bracket in inches

Limited Warranty, Warranty Exclusions, Limit of Liability and RMA Request Instructions

See the Desco Warranty -

[Desco.com/Limited-Warranty.aspx](https://www.desco.com/Limited-Warranty.aspx)



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.