



10069524-

AA B C D E V F F

AA	POSITION
04	2X20
06	2X30
08	2X40
10	2X50
12	2X60
14	2X70
16	2X80
18	2X90
20	2X100

B	FOR PLUG, SEE DWG. NO. 10069525			
COMBINATION OF MATED HEIGHT	Plug 1	Plug 2	Plug 3	Plug 4
Recep 1				
Recep 2				
Recep 3				
Recep 4				

NOTES:

- MATERIAL
HOUSING: LCP UL 94V-0
TERMINAL: NICKEL COPPER
- PLATING
AS SHOWN IN TABLE.
- SEE GS-12-547 FOR PRODUCT SPEC.
- SEE GS-14-551 AND GS-14-816 FOR THE DETAILS OF PACKAGING.
PRODUCT WILL BE PACKED IN ACCORDANCE TO GLOBAL PROCEDURE GS-14-920.
- PACKAGING OPTION 2: "NOT ALL SIZES AVAILABLE; CHECK WITH FACTORY".
- THIS PRODUCT MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THE HOUSING WITH STAND EXPOSURE UP TO 260° PEAK TEMPERATURE FOR 30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR REFLOW OVEN.
- PLATING OPTION "4" IS LEADFREE ALTERNATIVE FOR OPTION "0", AND OPTION "6" IS LEADFREE ALTERNATIVE FOR OPTION "1".
- THIS PARTNUMBER ONLY CATER FOR SPECIAL CUSTOMER REQUIREMENT OF COPLANARITY OF 0.1 FOR ALL POSITION.

V	MANDATORY CODE
/	STANDARD
H	FOR HUAWEI





E	PACKAGING
0	TUBE WITHOUT METAL CAP
2	T&R WITH METAL CAP
9	TUBE WITH METAL CAP

D	POLARIZATION PEG	HOLD DOWN
0	YES	NO
2	NO	NO

C	PLATING ON CONTACT AREA	FF
0	GOLD 0.2um MIN / TIN LEAD NICKEL UNDERPLATE OVERALL 1.27um MIN	NONE
1	GOLD FLASH (0.1um MIN) OVER PALLADIUM-NICKEL 0.76um MIN / TIN LEAD NICKEL UNDERPLATE OVERALL 1.27um MIN	NONE
4	GOLD 0.2um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF
5	GOLD 0.38um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF
6	GOLD FLASH (0.1um MIN) OVER PALLADIUM-NICKEL 0.76um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF
9	GOLD 0.2um MIN / GOLD 0.05um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF

mat'l. code				surface		tolerance		projection		product family			
				ISO 1302 ✓		ISO 406 ISO 1101				BERGSTAK HPL545			
ltr	ecn no	dr	date	tolerances unless otherwise specified				specified		title			
A	S06-0286	MCH	08/25/06	angles		linear		.0±.2				RECEPTACLE ASSY BERGSTAK 0.8MM	
B	S06-0316	MCH	09/25/06					.00±.15					
C	S09-0326	MCH	10/21/09	X'±2"				.000±.10		scale 1:1			
D	ELX-N-20407	Jim	03/26/15	dr	M. Cheong	08/25/06				dwg no			
E	ELX-N-28867	Bob	12/22/17	engr	Bob Gu	11/22/18				10069524		A3	
F	ELX-N-31885	Bob	11/22/18	chr	LQ Lei	11/22/18							
				appd	Tim Yao	11/22/18				type Product Customer Drawing			
sheet index	revision	E	F										
	sheet	1~6	1~6										


PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
10069524-041***	2X20	15.2	21.8	20.2
10069524-061***	2X30	23.2	29.8	28.2
10069524-081***	2X40	31.2	37.8	36.2
10069524-101***	2X50	39.2	45.8	44.2
10069524-121***	2X60	47.2	53.8	52.2
10069524-141***	2X70	55.2	61.8	60.2
10069524-161***	2X80	63.2	69.8	68.2
10069524-181***	2X90	71.2	77.8	76.2
10069524-201***	2X100	79.2	85.8	84.2




RECEPTACLE 1

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 1101	product family BERGSTAK HPL545			
ltr	ecn	no	dr	date	tolerances unless otherwise specified	mm	title RECEPTACLE ASSY BERGSTAK 0.8MM			
F					angles	linear	dwg no			
					X $\pm$ 2°	linear	sheet 2 of 6			
					dr	M. Cheong	size			
					engr	Bob Gu	A3			
					chr	LQ Lei	10069524			
					appd	Tim Yao	type Product Customer Drawing			
sheet index	revision	F								
	sheet	1~6								


RECEPTACLE 1



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X20, 2X30, 2X40, 2X50, 2X60






RECOMMENDED PCB LAYOUT WITHOUT PEGS



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X70, 2X80, 2X90, 2X100


mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 1101	product family BERGSTAK HPL545			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
F				angles	linear		RECEPTACLE ASSY BERGSTAK 0.8MM			
				X'±2'		scale 1:1	dwg no			
				dr	M. Cheong	08/25/06	sheet 3 of 6			
				engr	Bob Gu	11/22/18	10069524			
				chr	LQ Lei	11/22/18	A3			
				appd	Tim Yao	11/22/18	type Product Customer Drawing			
sheet index	revision	F								
	sheet	1~6								

PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
10069524-042***	2X20	15.2	21.8	20.2
10069524-062***	2X30	23.2	29.8	28.2
10069524-082***	2X40	31.2	37.8	36.2
10069524-102***	2X50	39.2	45.8	44.2
10069524-122***	2X60	47.2	53.8	52.2
10069524-142***	2X70	55.2	61.8	60.2
10069524-162***	2X80	63.2	69.8	68.2
10069524-182***	2X90	71.2	77.8	76.2
10069524-202***	2X100	79.2	85.8	84.2



COPLANARITY OF TAIL
0.1 MAX APPLIED TO 2X20 TO 2X100 PDS.




DETAIL C
SCALE 8:1



RECEPTACLE 2

mat'l. code				surface	ISO 1302	tolerance	ISO 406	ISO 1101	projection	product family			
ltr				ecn	no	dr	date	tolerances	unless otherwise specified	BERGSTAK HPL545			
F								angles	linear	title			
										RECEPTACLE ASSY			
								X±2'		BERGSTAK 0.8MM			
										dwg no			
								dr	M. Cheong	08/25/06	sheet4 of 6		
								engr	Bob Gu	11/22/18	size		
								chr	LQ Lei	11/22/18	10069524		
								appd	Tim Yao	11/22/18	A3		
											type		
											Product Customer Drawing		
sheet index	revision	F											
	sheet	1~6											


PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
10069524-043***	2X20	15.2	21.8	20.2
10069524-063***	2X30	23.2	29.8	28.2
10069524-083***	2X40	31.2	37.8	36.2
10069524-103***	2X50	39.2	45.8	44.2
10069524-123***	2X60	47.2	53.8	52.2
10069524-143***	2X70	55.2	61.8	60.2
10069524-163***	2X80	63.2	69.8	68.2
10069524-183***	2X90	71.2	77.8	76.2
10069524-203***	2X100	79.2	85.8	84.2




RECEPTACLE 3

mat'l. code				surface	ISO 1302	✓	tolerance	ISO 406	ISO 1101	projection	product family			
litr				ecn	no	dr	date	tolerances	unless	otherwise	BERGSTAK HPL545			
F								angles	linear	.0±.2	title			
								X'±2'		.00±.15	RECEPTACLE ASSY			
										.000±.10	BERGSTAK 0.8MM			
								dr	M. Cheong	08/25/06	dwg no			
								engr	Bob Gu	11/22/18	sheet5 of 6			
								chr	LQ Lei	11/22/18	size			
								appd	Tim Yao	11/22/18	10069524			
											type			
											Product Customer Drawing			
sheet	revision	F												
index	sheet	1~6												


RECEPTACLE 2 & 3



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X20, 2X30, 2X40, 2X50, 2X60



RECOMMENDED PCB LAYOUT WITHOUT PEGS AND HOLD DOWN



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X70, 2X80, 2X90, 2X100

mat'l. code				surface	ISO 1302	tolerance	ISO 406	ISO 1101	projection	product family
										BERGSTAK HPL545
ltr	ecn no	dr	date	tolerances unless otherwise specified						title
F				angles	linear	.0±.2			mm	RECEPTACLE ASSY
				X±2°		.00±.15				BERGSTAK 0.8MM
						.000±.10			scale 1:1	
				dr	M. Cheong	08/25/06				dwg no
				enr	Bob Gu	11/22/18				sheet 6 of 6
				chr	LQ Lei	11/22/18				size
				appd	Tim Yao	11/22/18				A3
sheet index	revision	F								type
	sheet	1~6								Product Customer Drawing



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.