

Manual Switches

Buttons/Lens for Switches and Indicators

AML51 Series


AML51 PUSHBUTTON ORDER GUIDE (All possible color combinations may not be available.)
For Incandescent or non-lighted display switches and pushbutton style indicators.

AML51-C

For AML11, 21, 31 switches and AML41 indicators:
Pushbutton Style


AML51-C

AML51-F

AML51-G

AML51-A

AML51-H

AML51-N*

AML51-B*

AML51-E*

AML51-M*

AML51-R*

For AML41D indicators only:
AML51-D

10

Display
Legend/Type

Transmitted Color
10 No legend
20 With legend
on cap.

Transmitted Color
(Clear cap and
color insert)
11 No legend
21 With legend
on insert

Dead Front
(Smoky gray cap
and color insert)
30 No legend
40 With legend
on insert

****Projected Color
(White cap and
color insert)
50 No legend
60 With legend
on cap

R

Full Color or
1st Color Split

R
Red
Y
Yellow
G
Green
B
Blue
W****
White
K***
Black
L***
Gray
A**
Amber

=

2nd
Color Split

R
Red
Y
Yellow
G
Green
B
Blue
W****
White
K***
Black
L***
Gray
A**
Amber

Example: **AML51-C10R**
Square full color button; with transmitted color,
no legend; red.

**Available with transmitted color and dead front only.
***Black and gray not recommended for lighted display.
†AML51-N buttons not available with Display/Legend Types
10 and 20.
Note: Dimensions include the .060 in bezel.

AML51 LENS ORDER GUIDE (All possible color combinations may not be available.)
For incandescent display AML41J, K, and L lens style indicators only.

AML51-J

Lens style

AML51-J

AML51-K

AML51-L

10

Display/Legend
Type

Transmitted Color
10 No legend
20 With legend

Transmitted Color
(Clear cap and
color insert)
11 No legend
21 With legend

Dead Front
(Smoky gray cap
and color insert)
30 No legend
40 With legend

****Projected Color
(White cap and
color insert)
50 No legend
60 With legend

R

Full Color
or 1st
Color Split

2nd
Color Split

3rd
Color Split

R
Red

Y
Yellow

G
Green

B
Blue

W****
White

A**
Amber

R
Red

Y
Yellow

G
Green

B
Blue

W****
White

A**
Amber

R
Red

Y
Yellow

G
Green

B
Blue

W****
White

A**
Amber

Example: **AML51-J10R**
Rectangular lens type button; full color;
transmitted color, no legend; red.

HOW TO ORDER BUTTON LEGENDS

When specifying legended buttons, submit a legend order sheet to cover each listing. To insure proper legend orientation, AML housings (when viewed from the panel front) should have the "MICRO SWITCH" identification facing UP on square devices and UP or to the LEFT on rectangular.

Button legend order sheets are shown on the following pages. Reproduce them on your office copier.

Legend Sheet

Form No.

AML51 Pushbuttons

FO-63394

AML51 Lens buttons

FO-63395

AML52 Pushbuttons

FO-63504

AML53 Paddle switch covers

FO-63567

AML55 Paddle switch covers

FO-63565

AML54 Rockers

FO-63566

AML56 Rockers




FO-63564

**Not available with projected color.
****Insert is clear for projected color when "W" is used.

42 Honeywell • Sensing and Control • 1-800-537-6945 USA • +1-815-235-6847 International • 1-800-737-3360 Canada

Buttons for Switches and Indicators

AML52 BUTTON ORDER GUIDE (All possible color combinations may not be available.)
For AML12, AML22 (w/o light pipe), AML32, AML42 LED display.

AML52-N	10	R
Button Type For LED Devices AML52-C  AML52-A*  For AML32 Neon Devices AML52-N 	Display/Legend Type Transmitted Color 10 No Legend 20 With Legend	Button Color R Red Y Yellow G Green B Blue W White K Black A Amber L Gray

Examples:
AML52-N10R
Rectangular full screen; for use on neon power switch with transmitted color, no legend; red button.

AML52-C10K
Square full screen; for use with LED device; transmitted color, no legend; black button.

Honeywell

AML 52/57 Pushbutton Legend Sheet/Product Specification
for L.E.D. & Neon Button

Page ___ of ___

Account No _____

Catalog Listing
AML52 -
Customer P.O. No.
MICRO SWITCH Sales Order
Customer Dwg. No.
Line Number
Schedule No.

Customer:
Address:

(city) (state)

Instructions

- 1. Fill in appropriate catalog listing - one listing/sheet.
2. Check proper figure #. Type size, type color.
3. Fill in quantity required.
4. Indicate legends desired — Do not exceed maximums shown in legend order guide.

Note

- 1. For Proper Legend Orientation, AML housings (when viewed from front of panel) should have "MICRO SWITCH" logo oriented "UP" on square devices and "UP" or to the "LEFT" on rectangular devices.
2. Please use black ink in filling out this form to help us process your order.

LEGEND ORDER GUIDE table with columns: Button: Type, Orientation, Figure NO, Max Lines (5/64, 7/64, 9/64, 13/64, 5/16), Max Characters (5/64, 7/64, 9/64, 13/64, 5/16)

Standard Legend Placement

- 1. Transmitted Color — Legend on outer shell (Button)
2. Figures 3 and 4 not applicable for AML57 listings

LEGEND ORDER CHART

LEGEND ORDER CHART table with columns: Customer Part NO, Fig NO, Type Size (5/64, 7/64, 9/64, 13/64, 5/16), Ink Color (Black, White), Button Qty, Legend Description (Left-to-Right or Top-to-Bottom), Sequence (1st Line, 2nd Line, 3rd Line)

FO-65604-D

Sheet Prepared By: _____ (Signature) _____ (Date)

A3 Modified Gothic
Modified Gothic lettering (A thru Z), numerals (0 thru 9) and Symbols below available in 5/64, 7/64, 9/64, 13/64 and 5/16.

SPECIAL LEGENDS
NOTE: Use this area to show special Legend Locations or Configurations NOT shown above. NON-STANDARD legends will involve additional charges and increased delivery time.

Honeywell

AML Pushbutton Legend Sheet/Product Specification

Account NO 126 - 284

Page of

LEGEND ORDER GUIDE

Table with columns: Button: Type, Orientation, Figure NO, Figure, Max Lines/Area, Max Characters/Line, and Max Characters/Line. It lists 9 button types (A*B, PR, C, D, E,H*, E,H*, F, G,N, M) and their specifications across various dimensions.

Definitions of Markings

Thru holes to snap into indicator housings
Internal reliefs to snap over switch plunger tabs

Standard Legend Placement -

- Use special legends sec. for other placements
1. Transmitted Color - Legend on outer shell (Button)
2. Dead Front - Legend on Insert
3. Projected Color - Legend on outer shell (Button)
4. Transmitted color with clear cap legend on insert

LEGEND ORDER CHART

Table with columns: Customer Part No, Fig No, Type Size, Ink Color, and But-ton Qty. It provides a structured way to order legends based on these parameters.

Form fields for Catalog Listing, AML51, Customer P.O. No., Customer Dwg. No., MICRO SWITCH Sales Order, Line Number, Schedule No., and Customer.

Form fields for Address (city, state) and Instructions.

- Instructions: 1. Fill in appropriate catalog listing - one listing/sheet. 2. Check proper figure #, Type size, Type color. 3. Fill in quantity required. 4. Indicate legends desired - Do not exceed maximums shown in legend order guide.
Note: 1. For Proper Legend Orientation, AML housings (when viewed from front of panel) should have "MICRO SWITCH" logo oriented "UP" on square devices and "UP" or to the "LEFT" on rectangular devices. 2. Please use black ink in filling out this form to help us process your order. 3. * INSERT ONLY ON STYLE A & H BUTTON

Form section for SPECIAL LEGENDS, A3 Modified Gothic, and STANDARD SYMBOLS AVAILABLE. Includes a table of symbols and their corresponding legend codes.

Form fields for Sheet prepared by (Signature) and (Date).

Manuals



AML Lens Legend Sheet/Product Specification

Account No _____ Page _____ of _____

LEGEND ORDER GUIDE

Button: Type Orientation	Figure No	Max Lines					Max Characters				
		5/64	7/64	9/64	13/64	5/16	5/64	7/64	9/64	13/64	5/16
AREA 1	J	4	4	3	3	2	1	14	11	10	7
	K	4	4	3	3	2	1	13	10	9	6
AREA 2	J	4	4	3	3	2	1	6	6	5	3
	K	4	4	3	3	2	1	5	5	4	3
AREA 3	J	4	4	3	3	2	1	4	3	3	2
	K	4	4	3	3	2	1	3	3	2	1
AREA 4	J	4	4	3	3	3	2	9	7	7	4
	K	4	4	3	3	3	2	8	7	6	3
AREA 5	J	3	3	2	2	1	1	8	7	6	4
	K	3	3	2	2	1	1	7	6	5	3
AREA 6	J	2	2	1	1	1	0	8	7	6	4
	K	2	2	1	1	1	0	7	6	5	3

Standard Legend Placement

- 1. Transmitted Color — Legend on outer shell (Button)
- 2. Dead Front - Legend on Insert
- 3. Projected Color - Legend on outer shell (Button)

LEGEND ORDER CHART

Customer Part No	Fig No	Type Size		Ink Color		But ton Qty	Legend Description			
		5/64	7/64	9/64	13/64	5/16	Black	White	Sequence: Left-to-Right or Top-to-Bottom	
									1st Line	2nd Line
									3rd Line	4th Line

Sheet Prepared By: _____

(Signature)

(Date)

Catalog Listing
AML51 —
Customer P.O. No. _____ Customer Dwg. No. _____
MICRO SWITCH Sales Order _____ Line Number _____ Schedule No. _____

Customer: _____
Address: _____ (city) _____ (state) _____

Instructions

- 1. Fill in appropriate catalog listing - one listing/sheet.
- 2. Check proper figure #, type size, type color.
- 3. Fill in quantity required.
- 4. Indicate legends desired — Do not exceed maximums shown in legend order guide.

Note

- 1. For Proper Legend Orientation, AML housings (when viewed from front of panel) should have "MICRO SWITCH" logo oriented "UP" on square devices and "UP" or to the "LEFT" on rectangular devices.
- 2. Please use black ink in filling out this form to help us process your order.

Modified Gothic lettering (A thru Z), numerals (0 thru 9) and Symbols below available in 5/64, 7/64, 9/64, 13/64 and 5/16.

A	B	C	D	E	F	G	H	I	J	K	L	M	N	O	P	Q	R	S	T	U	V	W	X	Y	Z	0	1	2	3	4	5	6	7	8	9	/	(	)	*	&																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
\$	¢	#	%	°	+	-	±	×	=	≠	>	<	→	↑	↓	←	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	⇀	⇁	⇂	⇃	⇄	⇅	⇆	⇇	⇈	⇉	⇊	⇋	⇌	⇍	⇎	⇏	⇐	⇑	⇒	⇓	⇔	⇕	⇖	⇗	⇘	⇙	⇚	⇛	⇜	⇝	⇞	⇟	⇠	⇡	⇢	⇣	⇤	⇥	⇦	⇧	⇨	⇩	⇪	⇫	⇬	⇭	⇮	⇯	⇰	⇱	⇲	⇳	⇴	⇵	⇶	⇷	⇸	⇹	⇺	⇻	⇼	⇽	⇾	⇿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗	↘	↙	↚	↛	↜	↝	↞	↠	↡	↢	↣	↤	↥	↦	↧	↨	↩	↪	↫	↬	↭	↮	↯	↰	↱	↲	↳	↴	↵	↶	↷	↸	↹	↺	↻	↼	↽	↾	↿	ↀ	ↁ	ↂ	Ↄ	ↄ	ↅ	ↆ	ↇ	ↈ	↉	↊	↋	↌	↍	↎	↏	←	↑	→	↓	↔	↕	↖	↗



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.