

IR Remote Control

P/N 559000105-3/559000106-3

Manual

Table of Contents

Introduction	3
Function Key definition	5
Dimensions	7
Specification	8
Contact Details	9

Introduction

The Digital View Remote control unit is compatible with all DV controller products. It is provided with universal control buttons that enable the control of OSD functions plus TV and media playback on DV media products.

Remote Control Unit (without DV Logo) : P/N 559000106-3,

Remote Control Unit (with DV Logo) : P/N 559000105-3,


- **Infra-red (IR)** - Supports IR control with DV remote control handset (P/N: 559000106-3). The IR sensor and cable kit (P/N: 446010401-3) are required.
- **Product Supported:**
 DV Controller: DD-2000, DVS-1600, SP-1600, SVH-1920, SVH-1920+, SVX-1920 and HE series controllers.
 DV Media Player: ViewStream™ 100, ViewStream™ 300, ViewStream™ 500, M3-100, M3-300, M3-310 & RM-DN5.
 DV VideoFlyers™ : ALL




- **Battery installation:**

- Remove the cover of the remote control
- Load the batteries (2 x AAA), make sure that they are in right position.
- Close the battery cover.


1. Open the battery cover.



2. Insert batteries



3. Close the battery cover



Note :


1. Do not subject the remote control to water and shock.
2. Remove the batteries if you will not use the remote control for an extended period of time.
3. Incorrect use of batteries may cause damage to the remote control unit. Read the battery instruction and use the batteries properly.
4. Do not use a new battery with an old one.
5. Do not heat, disassemble, short circuit or throw batteries into a fire.

CAUTION: Do not attempt to remove any part of the casing or internal parts.

Service & Warranty: Warranty is invalidated if the unit is dismantled in any way. The unit is not user serviceable or repairable.


2 Function Key explanations

Keys for DV Controller:



Key	Type / Use
1	Soft Power On/OFF
2	Swap input source
3	Zoom Image
4	Move Up/down/Left/Right (in OSD) & Hot Key
5	Previous OSD page
6	Direct hot key for signal source
7	(Attention + key "1") IR enable/Disable (SVH-1920, SVH-1920+ & SVX-1920 only)
8	Mute
9	PIP (SVH-1920, SVH-1920+ & SVX-1920 only)
10	Display information
11	Next OSD page
12	Volume Control

Keys for DV Player:



Key	Type / Use
13	Play
14	Stop
15	(Attention + Key "3") IR enable/disable
16	Track number (Direct access)
17	Mute
18	OSD On/Off
19	Previous track
20	Volume Control
21	Next track
22	Repeat
23	Pause

3 Dimensions



Notes:

- Dimensions are in mm.
- Drawing is not to scale.

4 Specifications

Operating voltage:	DC 3V
Operating voltage range:	DC 2.25V-3.6V
Operating temperature:	0° C ~ 45° C
Operating current:	≤30mA
Power source:	2 x AAA size batteries
Number of keys:	38
Oscillation frequency:	37.92KHz±3%
Arrival distance:	8 m
Accessories:	Infra-red sensor (446010401-3)(order separately), Batteries (AAA)
Dimensions :	158mm(H) x 45mm (W) x 21mm (D)
Weight:	Approx, 55g (without batteries)

CONTACT DETAILS

ASIA: Digital View Ltd
16th floor, Millennium City 3
370 Kwun Tong Road
Kwun Tong
Hong Kong

Tel: (852) 2861 3615
Sales: hksales@digitalview.com

Fax: (852) 2520 2987

EUROPE: Digital View Ltd
6 Marylebone Passage
London
W1W 8EX
UK

Tel: (44) (0)20 7631 2150
Sales: uksales@digitalview.com

Fax: (44) (0)20 7631 2156

USA: Digital View Inc.
18440 Technology Drive
Building 130
Morgan Hill, CA 95037

Tel: (1) 408-782 7773
Sales: ussales@digitalview.com

Fax: (1) 408-782 7883



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.