





A technical drawing of a 6-pin connector. The drawing shows a top-down view of the connector with six pins arranged in two rows of three. The pins are numbered 1 through 6. Pin 1 is the top-left pin, pin 2 is the top-middle pin, and pin 3 is the top-right pin. Pin 4 is the bottom-left pin, pin 5 is the bottom-middle pin, and pin 6 is the bottom-right pin. The drawing includes dimension lines and a grid to indicate the precise locations of the pins.



A technical line drawing of a rectangular metal safe. The safe's door is open to the right, revealing a heavy locking bolt on its edge. Inside the safe, there are two vertical compartments on the left, each containing three small drawers. To the right of these is a larger open space, and further right is a smaller compartment containing a single drawer. The safe has a sturdy, reinforced appearance with visible hinges and a locking handle on the door.

△-OS ITENS 1 E 2 SAO FORNECIDOS COMO MOSTRADO.
-ITEMS 1 AND 2 ARE SUPPLIED AS SHOWN.
△-VER DESENHO DE CLIENTE RESTRITO 444284-VW
-SEE RESTRICTED CUSTOMER DRAWING 444284-VW

GRAVAÇÃO MARKING
LOGOTIPO AMP AMP LOGO
CÓDIGO PAÍS PRODUTOR MANUFACTURER COUNTRY CODE
NOMENCLATURA MATERIAL MATERIAL NOMENCLATURE
NÚMERO COMPONENTE TYCO TYCO COMPONENT NUMBER
NÚMERO CAVIDADE CAVITY NUMBER
IDENTIFICAÇÃO CIRCUITO CIRCUIT IDENTIFICATION
LOGOTIPO CLIENTE CUSTOMER LOGO
NÚMERO PEÇA CLIENTE CUSTOMER PART NUMBER
PAÍS PRODUTOR MANUFACTURER COUNTRY
REV.+ LETRA REV.DA PEÇA REV.+ PART LETTER

	I	I	I	I	I	I	I									2	SPACER,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	AMARELO/YELLOW
I																I	HSG,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	CINZA/GRAY
	I															I	HSG,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	VERDE/GREEN
		I														I	HSG,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	BRANCO/WHITE
			I													I	HSG,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	AZUL/BLUE
				I												I	HSG,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	VIOLETA/VIOLET
					I											I	HSG,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	VERMELHO/RED
						I										I	HSG,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	MARROM/BROWN
							I									I	HSG,6POSN,JR P. TIMER/MIC TAB	P.A 6.6	PRETO/BLACK

REQUIRED PER ASSEMBLY										ITEM	DESCRIPTION	MATERIAL	FINISH			
1	2	3	4	5	6	7	8	9	10							
1	2	3	4	5	6	7	8	9	10							
444284																
THIS DRAWING IS UNCONTROLLED DOCUMENT FOR LOGO-ELECTRONICS CORPORATION IT IS SUBJECT TO THE LOGO-ELECTRONICS CORPORATION'S STANDARDIZATION DEPARTMENT SHOULD BE CONTACTED FOR THE LATEST REVISION.										DWN ML OGAWA 02JUL2004	 TYCO ELECTRONICS do Brasil LTDA. Sao Paulo, Brasil					
DIMENSIONS: mm 										CHN PL FARIA 02JUL2004		NAME HSG ASSEMBLY, 6 POSN, JR P TIMER/MIC TAB				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.1 1 PLC ±0.01 2 PLC ±0.001 3 PLC ±0.0001 4 PLC ±0.0001 ANGLES 1°										APVD MS OLIVEIRA 02JUL2004	PRODUCT SPEC - APPLICATION SPEC -	SIZE A 00779	CAGE CODE C=444284	DRAWING NO -	RESTRICTED TO -	
MATERIAL -										WEIGHT -						
CUSTOMER DRAWING										SCALE 4:1		SHEET 1	OF 1	REV D		



Компания «ЭлектроПласт» предлагает заключение долгосрочных отношений при поставках импортных электронных компонентов на взаимовыгодных условиях!

Наши преимущества:

- Оперативные поставки широкого спектра электронных компонентов отечественного и импортного производства напрямую от производителей и с крупнейших мировых складов;
- Поставка более 17-ти миллионов наименований электронных компонентов;
- Поставка сложных, дефицитных, либо снятых с производства позиций;
- Оперативные сроки поставки под заказ (от 5 рабочих дней);
- Экспресс доставка в любую точку России;
- Техническая поддержка проекта, помощь в подборе аналогов, поставка прототипов;
- Система менеджмента качества сертифицирована по Международному стандарту ISO 9001;
- Лицензия ФСБ на осуществление работ с использованием сведений, составляющих государственную тайну;
- Поставка специализированных компонентов (Xilinx, Altera, Analog Devices, Intersil, Interpoint, Microsemi, Aeroflex, Peregrine, Syfer, Eurofarad, Texas Instrument, Miteq, Cobham, E2V, MA-COM, Hittite, Mini-Circuits, General Dynamics и др.);

Помимо этого, одним из направлений компании «ЭлектроПласт» является направление «Источники питания». Мы предлагаем Вам помощь Конструкторского отдела:

- Подбор оптимального решения, техническое обоснование при выборе компонента;
- Подбор аналогов;
- Консультации по применению компонента;
- Поставка образцов и прототипов;
- Техническая поддержка проекта;
- Защита от снятия компонента с производства.



Как с нами связаться

Телефон: 8 (812) 309 58 32 (многоканальный)

Факс: 8 (812) 320-02-42

Электронная почта: org@eplast1.ru

Адрес: 198099, г. Санкт-Петербург, ул. Калинина, дом 2, корпус 4, литера А.